


Pass-Through and Cast-In Devices

3M™ Fire Barrier Devices

Fire barrier devices offer an effective one-piece solution for the firestopping of penetrating items through rated walls and floors. During a fire, these devices intumesce to form a seal, which helps protect against the spread of fire, smoke and toxic gases. Fire barrier devices are easy to install and are designed to take the guesswork out of firestopping. 3M offers pass-through options for walls and cast-in place options for poured concrete floors. 3M Fire Barrier Devices offer a simple, caulk-free, code compliant alternative to complicated caulk systems. Plus, they have the added benefit of retrofit firestop capabilities, which means less hassles after buildings are occupied.


3M™ Fire Barrier Pass-Through Devices



Caulk-free code-compliant devices designed for easy installation and re-enterability—perfect for firestopping structures where electrical, data and communication cables or plumbing pipes pass through fire-rated floors and walls.

- Available in 2" round, 2 1/2" square, 4" round and 4" square sizes
- UL classified L rating, hot and cold smoke seal
- Stackable for penetrant versatility
- Hinged for easy retrofit installation around cables
- UL classified 1, 2 and 3 hour fire (F) and temperature (T) ratings

3M™ Fire Barrier Pass-Through Mounting Brackets



Mounting brackets available for wall or floor mounting of 3M Fire Barrier Pass-Through Devices:

- Single mounting bracket available for all devices
- Triplex and Sixplex mounting brackets available for square devices

Specifications and Ordering Information for 3M™ Fire Barrier Pass-Through Products

Product	Description	Case Wgt	UPC (051115-)	Unit	Case Qty.
DEVICES AND BRACKET—ROUND					
PT2RD	2" Round Device	7.80	18773-5	Each	6
PT2RMB	2" Round Mounting Brackets (Pair)	11.0	18774-2	Pair	24
PT4RD	4" Round Device	12.39	16598-6	Each	6
PT4RMB	4" Round Mounting Brackets (Pair)	10.32	18754-4	Pair	24
DEVICES AND BRACKET—SQUARE					
PT2.5SD	2.5" Square Device	7.72	16596-2	Each	6
PT2.5SMB	2.5" Square Single Mounting Brackets (Pair)	11.60	18750-6	Pair	24
PT2.5TMB	2.5" Square Triple Mounting Brackets (Pair)	19.18	18751-3	Pair	24
PT4SD	4" Square Device	13.62	16597-9	Each	6
PT4SMB	4" Square Single Mounting Brackets (Pair)	16.40	18752-0	Pair	24
PT4SSB	4" Square Stud Bracket	8.20	18780-3	Each	24
PT4TMB	4" Square Triple Mounting Brackets (Pair)	29.10	18753-7	Pair	24
PT4SSMB	4" Square Sixplex Mounting Brackets (Pair)	36.00	18777-3	Pair	6