

Construction Tools

Tie-Wire Reel

- Rugged, lightweight reel is smooth aluminum alloy with wear parts made of steel.
- Feeds pre-coiled wire smoothly, easily, and quickly to save time and reduce wasted wire.
- Designed for left- or right-hand use.
- Large, comfortable rewind knob.
- Easily-removed cover plate that permits quick, convenient reloading to handle all types of wire.
- Optional accessory rigging-**leather** belt and hip pad available separately.



27400

Cat. No.	Diameter	Width	Weight (lbs.)
27400	6-1/4" (159 mm)	2-25/32" (71 mm)	2.35

Ironworker's heavy-duty tie-wire belts available. Tie-wire pad available.

Rebar Shear

- Top-loading 3/4" (19 mm) heavy-duty shear cuts up to and through #6 rebar.
- Easily replaceable tool-steel knives and heavy steel construction for long tool life.
- Includes mounting bolts, and removable steel handle. Does not include wooden platform.



64302K

Cat. No.	Handle Length	Shear Height	Shear Width	Shear Length	Weight (lbs.)
64302K	60" (152 cm)	6" (152 mm)	6" (152 mm)	13" (330 mm)	50.00

Replacement Cutting Blades

64321	pair of cutting blades for Cat. No. 64302K	.75
-------	--	-----

Rebar Hickeys



64308

- Lightweight rebar hickey has exceptionally durable steel-alloy head and extra-strong handle to withstand punishing service conditions.

Cat. No.	Hickey Size	Bends Rebar Size	Head Type and Bending Angle	Handle Length	Weight (lbs.)
64308	1	nos. 3 (.375" dia.), 4 (.500" dia.)	single 65°	24" (610 mm)	2.50
64309	1a	nos. 3 (.375" dia.), 4 (.500" dia.)	double 65° and 90°	24" (610 mm)	3.50
64310	2	no. 5 (.625" dia.)	single 65°	40" (1016 mm)	7.50
64311	3	no. 6 (.750" dia.)	single 65°	40" (1016 mm)	8.00
64312	4	nos. 7 (.875" dia.), 8 (1.00" dia.), 9 (1.128" dia.)	single 65°	60" (1524 mm)	16.40

Grizzly® Bar



64306

- A heavy, strong, multi-purpose tool that saves time and effort on the job.
- The 3" (76 mm) width protects concrete when stripping forms.
- Efficient blade angle and 55-1/2" (141 cm) total length provide high leverage as a crow bar and nail and spike puller.
- Blade is forged and hardened alloy with keyhole nail-pulling slot in center and V-notch in tapered edge.
- Very efficient nail-pulling tool even in awkward positions.
- Can be used to help align walls during tilt-up construction, to roll and align large pipe, to remove shingles and flooring, and for many other stripping and prying tasks.

Cat. No.	Overall Length	Weight (lbs.)
64306	55-1/2" (1410 mm)	12.00

All dimensions are in inches and (millimeters).

▲WARNING: Always wear approved eye protection.

▲WARNING: Always wear approved personal protective equipment.

▲WARNING: Do NOT exceed rated capacity for rebar shear and rebar hiccys.