

## Steel Tray

### Splice Plate

- Packaged in pairs with zinc-plated hardware
- Available in Pre-Galvanized (SPW), Hot-Dip Galvanized (SHW) and Stainless Steel 316 (SSW)



CAT. NO.	SIDE RAIL HEIGHT
(PREFIX)-3-SSP	3"
(PREFIX)-4-SSP	4"
(PREFIX)-5-SSP	5"
(PREFIX)-6-SSP	6"
(PREFIX)-7-SSP	7"

### Expansion Splice Plate


- Enables 1" expansion or contraction of tray system
- Packaged in pairs with hardware
- Available in Pre-Galvanized (SPW), Hot-Dip Galvanized (SHW) and Stainless Steel 316 (SSW)



CAT. NO.	SIDE RAIL HEIGHT
(PREFIX)-3-ESP	3"
(PREFIX)-4-ESP	4"
(PREFIX)-5-ESP	5"
(PREFIX)-6-ESP	6"
(PREFIX)-7-ESP	7"

### Step-Down Splice Plate

- Connects side rails of different heights
- Hardware included



CAT. NO.	MATERIAL PREFIX
(PREFIX)-(*)-(**)-SDS	SPW SHW SSW

(\*) Insert side rail height 1. (\*\*) Insert side rail height 2.  
**Note:** Side rail height 1 is greater than side rail height 2.

### Horizontal Adjustable Plate

- Adjustable hinge plates provide maximum horizontal installation flexibility
- Furnished in pairs with hardware
- Available in Pre-Galvanized (SPW), Hot-Dip Galvanized (SHW) and Stainless Steel 316 (SSW)



CAT. NO.	FOR TRAY WIDTHS
(PREFIX)-(*)06HAP	6"
(PREFIX)-(*)09HAP	9"
(PREFIX)-(*)12HAP	12"
(PREFIX)-(*)18HAP	18"
(PREFIX)-(*)24HAP	24"
(PREFIX)-(*)30HAP	30"
(PREFIX)-(*)36HAP	36"
(PREFIX)-(*)42HAP	42"

(\*) Insert side rail height.

### Vertical Adjustable Plate

- Provide maximum flexibility for changes in elevation
- Packaged in pairs with hardware
- Available in Pre-Galvanized (SPW), Hot-Dip Galvanized (SHW) and Stainless Steel 316 (SSW)



CAT. NO.	SIDE RAIL HEIGHT
(PREFIX)-3-VSP	3"
(PREFIX)-4-VSP	4"
(PREFIX)-5-VSP	5"
(PREFIX)-6-VSP	6"
(PREFIX)-7-VSP	7"

### Box to Tray Plates

- Secure tray to electrical panels or boxes, walls or end supports
- Packaged in pairs with hardware
- Available in Pre-Galvanized (SPW), Hot-Dip Galvanized (SHW) and Stainless Steel 316 (SSW)



CAT. NO.	SIDE RAIL HEIGHT
(PREFIX)-3-BSP	3"
(PREFIX)-4-BSP	4"
(PREFIX)-5-BSP	5"
(PREFIX)-6-BSP	6"
(PREFIX)-7-BSP	7"

### Closure End Plate

- Provides closure for any tray end
- Hardware included
- Available in Pre-Galvanized (SPW), Hot-Dip Galvanized (SHW) and Stainless Steel 316 (SSW)



CAT. NO.	SIDE RAIL HEIGHT
(PREFIX)-3-(*)-CEP	3"
(PREFIX)-4-(*)-CEP	4"
(PREFIX)-5-(*)-CEP	5"
(PREFIX)-6-(*)-CEP	6"
(PREFIX)-7-(*)-CEP	7"

\* Insert tray width.

### Reducing Splice Plate

- Used in pairs to provide a straight reduction or used with a Standard Splice Plate for an offset reduction
- One per package with hardware
- Available in Pre-Galvanized (SPW), Hot-Dip Galvanized (SHW) and Stainless Steel 316 (SSW)



CAT. NO.	SIDE RAIL HEIGHT
(PREFIX)-3-(*)-RSP	3"
(PREFIX)-4-(*)-RSP	4"
(PREFIX)-5-(*)-RSP	5"
(PREFIX)-6-(*)-RSP	6"
(PREFIX)-7-(*)-RSP	7"

\* For offset reduction: Insert width to be reduced.  
 For straight reduction: Insert 1/2 width to be reduced (two required).  
 Example: SPW-5-03-RSP = 3" offset reducer.

## One-Piece Tray

### Standard Splice Plate

- Packaged in pairs with zinc-plated hardware
- Provided as standard with each straight and/or fitting

CAT. NO.	SIDE RAIL HEIGHT
(PREFIX)-2-SSP	2"

Available in Aluminum (ALUW), Hot-Dip Galvanized (SHUW), Pre-Galvanized (SPUW) and Stainless Steel 316 (SSUW).

CAT. NO.	SIDE RAIL HEIGHT
(PREFIX)-3-SSP	3"
(PREFIX)-6-SSP	6"

Available in Aluminum (ALUW), Hot-Dip Galvanized (SHW), Pre-Galvanized (SPW) and Stainless Steel 316 (SSW).



### Expansion Splice Plate


- Allows for a 1" expansion or contraction of tray system
- Packaged in pairs with hardware

CAT. NO.	SIDE RAIL HEIGHT
(PREFIX)-2-ESP	2"

Available in Aluminum (ALUW), Hot-Dip Galvanized (SHUW), Pre-Galvanized (SPUW) and Stainless Steel 316 (SSUW).

CAT. NO.	SIDE RAIL HEIGHT
(PREFIX)-3-ESP	3"
(PREFIX)-6-ESP	6"

Available in Aluminum (ALUW), Hot-Dip Galvanized (SHW), Pre-Galvanized (SPW) and Stainless Steel 316 (SSW).




### Box to Tray Plates

- Designed to secure tray to electrical panels or boxes, walls or end supports
- Packaged in pairs with hardware

CAT. NO.	SIDE RAIL HEIGHT
(PREFIX)-3-BSP	3"
(PREFIX)-4-BSP	4"
(PREFIX)-5-BSP	5"
(PREFIX)-6-BSP	6"
(PREFIX)-7-BSP	7"

Available in Pre-Galvanized (SPW), Hot-Dip Galvanized (SHW) and Stainless Steel 316 (SSW)



### Horizontal Adjustable Plate

- Adjustable hinge plates provide maximum horizontal installation flexibility
- Furnished as a kit with hardware

CAT. NO.	WIDTH
(PREFIX)-(*)06HAP	06"
(PREFIX)-(*)09HAP	09"
(PREFIX)-(*)12HAP	12"
(PREFIX)-(*)18HAP	18"
(PREFIX)-(*)24HAP	24"
(PREFIX)-(*)30HAP	30"
(PREFIX)-(*)36HAP	36"

\* Insert side rail height.

Available in Aluminum (ALUW), Pre-Galvanized (SPUW) and Stainless Steel 316 (SSUW)

