

Utility Boxes and Covers



CI1141



BC1110



CI1110-SB



BC1110-LSKO



BC1110-SSX



BC1110-R



BC1151

BC1151: For toggle switch.



BC1199

BC1199: For duplex receptacle.



BC11-C-1



BC11-C-2



BC11-C-3



BC11-C-4



BC11-C-5



BC11-C-10



CI11-C-10-HV



BC11-C-4-HV



BC11-C-5-HV



Cat. No.	Volume (Cu. in.)	Features		Knockouts		
		Bracket	Raised Ground Screw	1/2 in. ends	1/2 in. bottom	1/2 in. sides
1-1/2 in. Deep – 4 in. x 2-1/4 in.						
CI1141	13.0	mounting lugs	no	2	2	6
1-7/8 in. Deep – 4 in. x 2-3/8 in.						
BC1110	16.5	-	yes	2	2	6
CI1110-SB	16.5	"SB"	yes	2	2	3
BC1110-R	16.5	-	-	2	-	6
2-1/8 in. Deep – 4 in. x 2-1/2 in.						
BC1151	18.5	-	no	2	2	-
BC1199	18.5	-	no	2	2	-
1-7/8 in. Deep – 4 in. x 2-3/8 in.						
BC1110-LSKO	16.5	-	yes	2	2	-
BC1110-SSX	16.5	"SSX"	yes	2	2	-

Cat. No.	Description	Cat. No.	Description
Covers – 11 Series			
BC11-C-1	For duplex receptacle	BC11-C-10	Decora/GFCI
BC11-C-2	For 1-19/32 in. diameter 20 A single locking receptacle	CI11-C-10-HV	Decora 347 volt
BC11-C-3	For 1-13/32 in. diameter 15 A single receptacle	BC11-C-4-HV	Blank 347 volt
BC11-C-4	Blank	BC11-C-5-HV	For toggle switch
BC11-C-5	For toggle switch 347 volt	Note: Covers: Device mounting screws included	

Steel Stud Boxes


4 in. and 4-11/16 in. Square Boxes and 4 in. Octagonal Boxes




BC52151-KSSX




BC52171-KSSX



CI52171-KSSX-1



CI52171-1-SSX-1



CI72171-KSSX



CI54151-KSSX



BC54151-LSSAX



BC1110-SSX



CI54171-KSSX



BC52171-KSSXHVKIT



Cat. No.	Volume (Cu. in.)	Features		Knockouts					Pryouts sides
		Clamps	Raised Ground Screw	1/2 in. sides	1/2 in. bottom	3/4 in. sides	3/4 in. bottom	1 in. sides	
4 in. Square Boxes – 1-1/2 in. Deep									
BC52151-KSSX	21.0	-	yes	7	4	3	2	-	-
4 in. Square Boxes – 2-1/8 in. Deep									
BC52171-KSSX	30.0	-	yes	7	4	3	2	-	-
CI52171-KSSX-1	30.0	-	yes	7	4	3	2	-	-
CI52171-1-SSX-1	30.0	-	yes	-	4	-	2	2	-
4-11/16 in. Square Boxes – 2-1/8 in. Deep									
CI72171-KSSX	42.0	-	yes	8	4	4	2	-	-
4 in. Octagonal Boxes – 1-1/2 in. Deep									
CI54151-KSSX	15.0	-	yes	2	4	2	2	-	-
BC54151-LSSAX	15.0	loomex/BX	-	-	1	-	-	-	4
4 in. Octagonal Boxes – 2-1/8 in. Deep									
CI54171-KSSX	21.0	-	yes	2	4	2	2	-	-
4 in. Square – 2-1/8 in. Deep									
BC52171-KSSXHVKIT	33.6	"SSX"	yes	6	-	2	-	-	-

Cat. No.	Volume (Cu. in.)	Features		Knockouts		
		Brackets	Raised Ground Screw	1/2 in. ends	1/2 in. bottom	1/2 in. sides
4 in. Square Boxes – 1-1/2 in. Deep						
BC1110-SSX	16.5	"SSX"	yes	7	4	3