


# SWITCHES

## PlugTail™ Specification Grade Decorator Switches


### PT2626W

#### PlugTail™ Decorator Switches

- A. Auto-ground clip** assures positive ground.
  - B. Heavy-gauge steel strap** for superior strength.
  - C. No exposed terminals** create a finger-safe application before, during, and after installation.
  - D. Built-in connector** features large brass terminal blades to ensure consistent, reliable electrical connections.
  - E. Large brass contacts** snugly terminate on device blade terminals. Audible snapping latch assures connection, allows release.
  - F. Polycarbonate connector housing** secures terminations and conductors in a UL Listed, finger-safe housing.
  - G. WAGO push-in connectors** are available to further speed up installation.
- Shallow design** for easier installation.




PT2626W




# SWITCHES


## PlugTail™ Specification Grade Decorator Switches 15 & 20A, 120/277VAC




PT2621W



PTS6STR3 PTS6STR4



PTS6STR3BP PTS6STR4BP



PTJ

CATALOG NUMBER		RATING		COLOR	3rd PARTY COMPLIANCE		
SINGLE POLE	THREE-WAY	A.	VAC		UL20	FSUL WS896	CSA C22.2 111
<b>DECORATOR SWITCHES</b>							
PT2601I	PT2603I	15	120/277	Ivory	•	•	•
PT2601W	PT2603W	15	120/277	White	•	•	•
PT2601	PT2603	15	120/277	Brown	•	•	•
PT2601GRY	PT2603GRY	15	120/277	Gray	•	•	•
PT2601RED	PT2603RED	15	120/277	Red	•	•	•
PT2601BK	PT2603BK	15	120/277	Black	•	•	•
PT2601LA	PT2603LA	15	120/277	Light Almond	•	•	•
PT2621I	PT2623I	20	120/277	Ivory	•	•	•
PT2621W	PT2623W	20	120/277	White	•	•	•
PT2621	PT2623	20	120/277	Brown	•	•	•
PT2621GRY	PT2623GRY	20	120/277	Gray	•	•	•
PT2621RED	PT2623RED	20	120/277	Red	•	•	•
PT2621BK	PT2623BK	20	120/277	Black	•	•	•
PT2621LA	PT2623LA	20	120/277	Light Almond	•	•	•
<b>ILLUMINATED DECORATOR SWITCHES</b>							
PT2625I	PT2626I	20	120/277	Ivory	•	•	•
PT2625W	PT2626W	20	120/277	White	•	•	•
PT2625BK	PT2626BK	20	120/277	Black	•	•	•
PT2625LA	PT2626LA	20	120/277	Light Almond	•	•	•

Available in 347VAC Canadian Catalog Numbers, add 347 to the end of the Catalog Number.  
 Example: PT2601W347. All Canadian Products have Combination Slotted/Robertson Head Brass Screws.

CATALOG NUMBER	WIRE TYPE	WIRE LENGTH	WIRE COLORS
<b>PLUGTAIL CONNECTORS FOR SINGLE POLE SWITCHES</b>			
PTS6STR3	3 Wire Stranded	6"	Green, Black, Black
PTS6SOL3	3 Wire Solid	6"	Green, Black, Black
PTS6STR3277	3 Wire Stranded	6"	Green, Brown, Brown
PTS6SOL3277	3 Wire Solid	6"	Green, Brown, Brown
<b>PLUGTAIL CONNECTORS FOR THREE-WAY SWITCHES</b>			
PTS6STR4	4 Wire Stranded	6"	Green, Red, Red, Black
PTS6SOL4	4 Wire Solid	6"	Green, Red, Red, Black
PTS6STR4277	4 Wire Stranded	6"	Green, Brown, Yellow, Yellow
PTS6SOL4277	4 Wire Solid	6"	Green, Brown, Yellow, Yellow
<b>PLUGTAIL CONNECTORS FOR SINGLE POLE SWITCHES WITH WAGO CONNECTORS</b>			
PTS6STR3BP	3 Wire Stranded	6"	Green, Black, Black
PTS6SOL3BP	3 Wire Solid	6"	Green, Black, Black
PTS6STR3277BP	3 Wire Stranded	6"	Green, Brown, Brown
PTS6SOL3277BP	3 Wire Solid	6"	Green, Brown, Brown
<b>PLUGTAIL CONNECTORS FOR THREE-WAY SWITCHES WITH WAGO CONNECTORS</b>			
PTS6STR4BP	4 Wire Stranded	6"	Green, Red, Red, Black
PTS6SOL4BP	4 Wire Solid	6"	Green, Red, Red, Black
PTS6STR4277BP	4 Wire Stranded	6"	Green, Brown, Yellow, Yellow
PTS6SOL4277BP	4 Wire Solid	6"	Green, Brown, Yellow, Yellow

All PTS Connectors are 120/277VAC


CATALOG NUMBER	DESCRIPTION
<b>PLUGTAIL JUMPER</b>	
PTJ	PlugTail Cover for Rough In
PTJ5	PlugTail Cover for Rough In, 5-pack

All devices listed on this page conform to NEMA WD-1 and WD-6.


# DEVICES & WALL PLATES

## Color Selection Chart

### Devices & Plastic Wall Plate Colors



Ivory    Light Almond    White    Green    Antique Brass    Dark Bronze    Nickel




Black    Blue    Brown    Gray    Orange    Red

See specific device and wall plate catalog charts for particular color availabilities.

### Metal Wall Plates


Metal Finish



Aluminum    Brass (Brushed)    Polished Brass    Stainless Steel    Brushed Bronze    Chrome

### Custom Metal Wall Plates Paint Finish Colors

Paint Color



Orange    Green    Gray    Yellow    Glossy Black    Brown    White



Primer    Red    Pink    Flat Black    Ivory    Light Almond    Blue

To order custom metal wall plates, see Pages P-41 – P-45.

**For additional colors consult factory.**

All devices listed on this page conform to NEMA WD-1 and WD-6.