



OMNIBOX™ SERIES FLOOR BOXES

Omnibox Series Nonmetallic Cover Plate Flanges Ordering Information (continued)


837PCC 3-Gang Nonmetallic Carpet Flange**837PCC-BLK, 837PCC-BRN**

For Ortronics® connectivity use with 829PFLRT Cover. For Activate™ connectivity use with 829PFL Cover. Accepts Ortronics® MAB6TJ TracJack and MAB3S2 Series II adapters and Wiremold CM Series inserts, sold separately.


Omnibox Series Nonmetallic Cover Plates Ordering Information

828PR Nonmetallic Duplex Cover Plate**828PR-BLK, 828PR-BRN**


Flip lids. Can also be used with a 106 type communication adapter.

829PFLRT**Nonmetallic Communication Cover Plate****9829PFLRT-BLK, 829PFLRT-BRN**


Individual flip lids. Gasket included. Ortronics® MAB6TJ TracJack and MAB3S2 Series II adapters included.

828PRGFI Nonmetallic GFI Cover Plate**828PRGFI-BLK, 828PRGFI-BRN**


May be used with Ortronics® Connectivity systems in conjunction with 817, 827 and 837PCC Series flanges.

829PCK Nonmetallic Communications Cover Plate**829PCK-BLK, 829PCK-BRN**

Breakouts. Feed through only, not for use with a mounting plate for communication jacks.

829PFL Nonmetallic Communication Cover Plate**829PFL-BLK, 829PFL-BRN**

Individual flip lids. Gasket included. Wiremold CM Series inserts included.

829PSTC Nonmetallic Communications Cover Plate**829PSTC-BLK, 829PSTC-BRN**

Data slides. Feed through only, not for use with a mounting plate for communication jacks.

NOTE: UL Listed for tile, terrazzo, and carpet floors. Brass covers and flanges are not interchangeable with aluminum or nonmetallic covers and flanges. Nonmetallic covers are interchangeable with aluminum flanges.

WALKERDUCT® UNDERFLOOR DUCT SYSTEMS

Walkerduct Underfloor Duct Systems Service Fitting Compatibility

PRODUCT FAMILY	CATALOG NUMBER	ACTIVATION LOCATION		SERVICE CAPACITY			SERVICE COMPATIBILITY			MATERIAL/COLORS				
		Flush	Pedestal	Single Service	Dual Service	Triple Service	Power	Communication	Audio/Visual	Polycarbonate	Aluminum	Brass	Gray	Black
	817B	•		•			•	•				•		
	827B	•			•		•	•				•		
	837B	•				•	•	•				•		
	817PCC	•		•			•	•		•				•
	827PCC	•			•		•	•		•				•
	837PCC	•				•	•	•		•				•
	818TCAL	•		•			•	•			•			
	828TCAL	•			•		•	•			•			
	838TCAL	•					•	•	•		•			
	S165B	•		•			•					•		
	S165BLK/BRN	•		•						•				•
	S166B	•		•				•				•		
	S166BLK/BRN	•		•				•		•				•
	S175BLK/BRN	•		•			•			•				•
	PSRC9TC	•		•			•				•	•	•	•
	PSRC9AMDTC	•		•				•			•	•	•	•
	PSRC9FFTC	•		•				•			•	•	•	•
	1204BF		•	•				•				•		
	1204AL		•	•				•			•			
	1223BF		•	•			•					•		
	1223AL		•	•			•				•			
	MP4		•	•			•	•	•		•			
	MP8		•		•		•	•	•		•			
	MP8-1		•		•		•	•	•		•			
	525A		•	•				•	•		•			
	525B		•	•				•	•		•			
	525C		•	•				•	•		•			
	525D		•	•				•	•		•			
	525F		•	•			•				•			
	25G		•	•			•				•			
	525H		•	•			•				•			
	525I		•	•			•				•			
	525J		•	•			•	•	•		•			
	525RT		•	•				•			•			
525ACT		•	•					•		•				