


RESIDENTIAL DIMMERS & FAN SPEED CONTROLS

Harmony® Multi-Location Dimmers



H703PMMTUW

Features


- Multi-location dimming compatible with 3-way wiring for simple installation
- Supports up to 10 locations with remote dimmers
- **Interchangeable Face Versions**
 - Package comes with three face colors – Ivory, White, Light Almond (TC).
 - White only option also available.
 - Interchangeable faces available in nine colors (sold separately, see below).

CATALOG NUMBER	DESCRIPTION	RATINGS	COLOR
TRU-UNIVERSAL MULTI-LOCATION MASTER DIMMER			
H703PMMTUTC	Single Pole/3-Way with Preset, 3 Interchangeable Face Plates	120V, 60Hz; Incandescent, Halogen, ELV - 700W; MLV - 500VA; LED/CFL - 450W; EFL - 5.5A	Ivory/Light Almond/White
H703PMMTUW	Single Pole/3-Way with Preset		White
CFL/LED MULTI-LOCATION MASTER DIMMER			
HCL453PMMTC	Single Pole/3-Way with Preset, 3 Interchangeable Face Plates	120V, 60Hz, 450W	Ivory, Light Almond, White
HCL453PMMW	Single Pole/3-Way with Preset		White
SINGLE POLE/3-WAY DE-HUMMER MULTI-LOCATION MASTER FAN SPEED CONTROL WITH PRESET			
HDH163PMMTC	Single Pole/3-Way, DeHummer, 3 Interchangeable Face Plates	120V, 1.6A	Ivory, Light Almond, White
HDH163PMMW	Single Pole/3-Way, DeHummer, Preset		White
SINGLE POLE/3-WAY MULTI-LOCATION REMOTE DIMMER, SINGLE POLE/3-WAY, DEHUMMER, PRESET			
HMRTC	Single Pole/3-Way, 3 Interchangeable Face Plates	120V	Ivory, Light Almond, White
HMRW	Single Pole/3-Way		White
MULTI-LOCATION DIMMER INTERCHANGEABLE FACE PLATE, SINGLE POLE/3-WAY			
HMKITAB	Harmony® Interchangeable Face Plates for Multi-Location Master Dimmers		Antique Brass
HMKITBK			Black
HMKIT			Brown
HMKITDB			Dark Bronze
HMKITGRY			Gray
HMKITI			Ivory
HMKITLA			Light Almond
HMKITNI			Nickel
HMKITW			White
MULTI-LOCATION DE-HUMMER FAN SPEED CONTROL INTERCHANGEABLE FACE PLATE			
HDHKITAB	Harmony® Interchangeable Face Plates for Multi-Location Master Fan Speed Controls		Antique Brass
HDHKITBK			Black
HDHKIT			Brown
HDHKITDB			Dark Bronze
HDHKITGRY			Gray
HDHKITI			Ivory
HDHKITLA			Light Almond
HDHKITNI			Nickel
HDHKITW			White
MULTI-LOCATION REMOTE DIMMER INTERCHANGEABLE FACE PLATE			
HMRKITAB	Harmony® Interchangeable Face Plates for Multi-Location Remote Dimmers		Antique Brass
HMRKITBK			Black
HMRKIT			Brown
HMRKITDB			Dark Bronze
HMRKITGRY			Gray
HMRKITI			Ivory
HMRKITLA			Light Almond
HMRKITNI			Nickel
HMRKITW			White

DEVICES & WALL PLATES

Color Selection Chart

Devices & Plastic Wall Plate Colors



Ivory

Light Almond


White

Green

Antique Brass

Dark Bronze

Nickel



Black

Blue

Brown

Gray


Orange

Red

See specific device and wall plate catalog charts for particular color availabilities.

Metal Wall Plates

Metal Finish



Aluminum

Brass (Brushed)

Polished Brass


Stainless Steel

Brushed Bronze

Chrome

Custom Metal Wall Plates Paint Finish Colors

Paint Color



Orange

Green

Gray

Yellow

Glossy Black

Brown

White



Primer

Red

Pink

Flat Black

Ivory

Light Almond

Blue

To order custom metal wall plates, see Pages P-40 – P-42.

For additional colors consult factory.