Panelboards

Modifications, Additions Replacements for Fusible Switches

Selection

Replacement Units 12

Amperes Rating	250 Volts® Code Fuses Cat. No.	600 Volts® Code Fuses Cat. No.	600 Volts J Fuses Cat. No.	600 Volts [®] R Fuses Cat. No.	600 Volts® T Fuses Cat. No.	600 Volts C Fuses Cat. No.	Height in (mm)
VK Switch Fo	VK Switch For Use With FPP6 Panelboards®30®						
30/30	N/A	N/A	VK23611JP	VK23611RP	N/A	VK23611CP	6.25 (159)
60/60	N/A	N/A	VK23622JP	VK23622RP	N/A	VK23622CP	6.25 (159)
100/100	N/A	N/A	VK33633JP	N/A	VK33633TP	VK33633CP	7.5 (90)
200/200	N/A	N/A	VK73644JP	N/A	VK73644TP	N/A	10 (254)

VB Switch Fo	VB Switch For Use With VB6 Panelboards						
30/30 60/60 100/100 200 400 600	N/A N/A N/A N/A V7F3204CP V7H3205CP V7H3206CP	N/A N/A N/A V7F3604CP V7H3605CP V7H3606CP	V7E3611JP V7E3622JP V7E3633JP V7F3604JP V7H3605JP V7H3606JP	N/A N/A N/A V7F3604RP V7H3605RP V7H3606RP	N/A N/A N/A N/A V7H3605TP V7H3606TP	N/A N/A N/A N/A N/A	7.5(190) 7.5(190) 7.5(190) 10(254) 15(381) 15(381)

Connecting Strap Kits

Rating Amperes	VB Switch VB6 [®] Cat. No.	VK Switch Series 6 Cat. No.
30/30 60/60 100/100	VB6-71	VK6-57 VK6-57 VK6-58
100 200/200 200 400-600	VB6-71 N/A VB6-71 VB6-150	N/A VK6-72 VK6-71 [©] N/A

Panelboard				
Tub Width Depth		Panel Type	Replacement Max Amps	Note
	9″	OLD CDP	400	MCCB only.
30" - 36" - 42"	9.75"	OLD CDP	600	MCCB only.
32" - 38"	13.75"	CDP/VB6	1200A	MCCB series 6 connectors
			600A	"VB" style units only (*)
38"	12.75" SPP/FPP6	1200A	MCCB series 6 connectors	
			600A	"VK" or "VB" style (*)

Blank Plates®

For use with Series 6 CDP Panelboards, S5, F2, FCI and FCII Switchboards.		
	SPP/FPP/CDP/VB	
Height	6	
1.25"	6FPB01	
2.50"	6FPB02	
3.75"	6FPB03	
5.00"	6FPB05	
10.00"	6FPB10	
15.00"	6FPB15	

① For Series 6 Main Devices above 200A, add suffix MS to Catalog Number when ordering.

② When 2-Pole units are required, use 3-Pole.

③ Series 6 (VB6, CDP6) replacement units and connector kits

also accommodates FCI and FCII distributions interiors. Units installed after October 1991 will be FPP6 type.

® Refer to Siemens for units equipped with auxiliary switches.

⑤ Price is for two brackets – to be included with filler plates.

[©] To be used in tubs with 30-200A, VB units or fillers in 12⁵/8" deep tub.

② Can be used as fillers or in place of circuit breakers, VK or VB Switches.

Special order