

Digital Audio Four-Room, Multi-Source Kit, White

AU7254-WH



The AU7254-WH is a four-room, multi-source Digital Audio Kit. Conveniently supplying all of the core components necessary to install a four-room Digital Audio system with digital and analog source accessibility, this kit comes complete with (4) [AU7010-WH](#) Digital Audio Amplified Keypads, (1) [AU7000](#) Digital Audio Distribution Module, (1) [AU7001](#) Digital Audio Input Module, (1) [AU7007-WH](#) Digital Audio Global Source Input, (1) [PW1020](#) Digital Audio Power Distribution Module, (1) [PW1060](#) Power Supply, and (1) [PW7760](#) Power Supply.

features & benefits

- Comes complete with all core components for a four-room, multi-source Digital Audio System with digital and analog source accessibility
- Provides access to streaming services such as: Pandora, Rhapsody, Napster, SiriusXM, TuneIn, and Deezer
- Allows streaming of networked digital content from iTunes, Windows Media Player libraries, and mobile devices
- Offers global access to analog source equipment
- Provides 20 watts of Class D power per zone
- Conveniently controllable through both included keypads as well as free, intuitive Android or iOS apps for smartphones and tablets
- Provides all core components needed to install a four-room, multi-source Digital Audio System with digital and analog source accessibility
- Structured wiring based to offer easy installation and a repeatable solution
- Simple setup using smartphone or tablet, no PC required
- Available in a two-room kit ([AU7152-WH](#))

specifications

General Info

Cable Type: Connect Cat5e or better and speaker wire 18-16 gauge.

Color: White

Size: 11.25" x 7.75" x 14.5"

Termination: 1264.22 cu. in.

Connection Type: RJ45 connections and removeable pheonix screw down terminals
Type: Low Voltage, Audio System
Housing Material: Plastic/Metal
Special Features: 4-Zone, 2-Source Digital Audio System
Style: Decorator Keypad; Structured wiring cabinet (not included)

Listing Agencies/Third Party Information

RoHS: Yes
FCC Standard: Yes
UL Standard: Yes

Dimensions

Depth U S: 14.5"
Width U S: 11.25"
Primary Packaging Weight Metric: 2.99 kg
Primary Package Weight U S: 6.6 lbs
Product Weight Metric: 2.99 kg
Product Weight U S: 6.6 lbs
Volume: 1264.22 cu. in.
Weight: 6.6 lbs
Height: 7.75"

Technical Information

Connection Method: Ethernet network
Mounting: Wall Mount/Enclosure Mount
Power Requirements: 24 VDC 60W Power Supply / 12 VDC 18W Power Supply
Supported Standards: FCC, UL, RoHS
Watts: 20W 8Ω
Connection Location: Data Control Interface: Ethernet/Digital Keypad
Source Inputs: 2-Sources
Source Outputs: 4-Zones

Buy American Act Compliance

Country of Origin: CHINA