

UNIDUCT® 2800 SERIES RACEWAYS

Ordering Information


Uniduct® 2800 Series Raceway Wire Fill Capacities for Communications

		O.D. (Approx. Dia.)		40%
	CABLE/WIRE SIZE	Inches	[]	FILL
UNSHIELDED TWISTED PAIR	4-pair, 24 AWG, Cat 3	0.190	[4.8]	4
	4-pair, 24 AWG, Cat 5e	0.210	[5.3]	3
	4-pair, 24 AWG, Cat 6	0.250	[6.3]	2
	4-pair, 24 AWG, Cat 6a*	0.354	[9.0]	1
	25-pair, 24 AWG	0.410	[10.4]	1
COAXIAL	RG6/U	0.270	[6.9]	2
FIBER	ZipCord	0.118 x 0.236	[3 x 6]	4
	Round 4 Strand Fiber	0.187	[4.8]	4
	Round 6 Strand Fiber	0.256	[6.5]	2

NOTE: For additional information, refer to the Technical Section.

* Category 6 augmented (6a) cable for 10 gigabit ethernet – max allowed cable diameter per addenda No. 11 ANSI TIA/EIA 568-B.2.

2800, 2800L8 One-Piece Latching Raceway



Co-extruded design, smooth ivory plastic finish with adhesive backing. 2800 available in 6' [1.8m] lengths, packed 120' [36.6m] per carton. 2800L8 available in 8' [2.44m] length, packed 160' [48.8m] per carton. Also available in white (2800-WH, 2800L8-WH).

PVC-1 PVC Raceway Cutter



Regular duty cutter. Ideal for use with small nonmetallic raceways.

2806 Cover Clip



Covers seam where two pieces of 2800 Series Raceway Cover come together. Also available in white (2806-WH).

2810B Blank End Fitting



Closes off end of 2800 Series Raceway. Also available in white (2810B-WH).


NOTE: Device Boxes for Uniduct 2700 Series Raceway can be found on pages located at the end of this product section.

2811 Flat Elbow




Makes right angle turns in 2800 Series Raceway on same surface. Also available in white (2811-WH).

2811FO Radiused Flat Elbow




Makes right angle turns in 2800 Series Raceway on same surface. Maintains 1 1/4" [32mm] bend radius when installing UTP and fiber optic cable. Also available in white (2811F0-WH).

2815 Tee




For branching of 2800 Series Raceway running at right angles. Also available in white (2815-WH).

2815FO Radiused Tee




For branching of 2800 Series Raceway running at right angles. Maintains 1 1/4" [32mm] cable bend radius when installing UTP and fiber optic cable. Also available in white (2815FO-WH).

2817 Internal Elbow



For right angle turns around internal corners. Also available in white (2817-WH).

2817FO Radiused Internal Elbow



Makes right angle turns around internal corners of 2800 Series Raceway. Maintains 1 1/4" [32mm] bend radius when installing UTP and fiber optic cable. Also available in white (2817FO-WH).