









Device Boxes

Conduit Knockouts

			
CI1104-K	BC1104-LE	CI1104-SB	BCR2000
Concentric knockouts. Recessed ears.	Less ears.		
			
CI3104-KSSX	BC3104-KSS1X-1	CI3104-SSX	CI1004
Concentric knockouts. "Wraparound" bracket for 2-1/2 in. and 3-5/8 in. steel studs. With integral support bracket.	Concentric knockouts. "Wraparound" bracket for 2-1/2 in. and 3-5/8 in. steel studs. With integral support bracket. Brackets positioned for 2 layers of 1/2 in. Drywall.	"Wraparound" bracket for 2-1/2 in. and 3-5/8 in. steel studs. With integral support bracket.	Recessed ears.



Cat. No.	Volume (Cu. in.)	Features		Knockouts		
		Ears	Bracket	1/2 in. ends	1/2 in. bottom	3/4 in. ends
2 in. Deep — Gangable — 3 in. x 2 in.						
CI1104-K	12.5	recessed	-	2	2	2
BC1104-LE	12.5	-	-	2	2	-
CI1104-SB	12.5	-	"SB"	2	2	-
CI3104-KSSX	16.0	-	"SSX"	2	2	2
BC3104-KSS1X-1	16.0	-	"SSX"	2	2	2
CI3104-SSX	16.0	-	"SSX"	2	2	-
3 in. Deep — Gangable — 3 in. x 2 in.						
CI1004	15.0	recessed	-	2	2	-
CI3004-KSSX-1.25	18.0	-	"SSX"	-	1	2


Cat. No.	Volume (Cu. in.)	Usage	Ground Screw	Knockout
2 in. Deep — Non-Gangable — 3-3/4 in. x 4 in. x 2 in.				
BCR2000*	18.0	K0	2	2

*Supplied c/w one CI4004 connector




Steel Stud Boxes


Device Boxes




CI3104-KSSX




BC3104-KSS1X-1




BC3104-LSSAX




BC3104-LSSX




CI3104-LSS1X-1




CI3104-LSSA1X-1



CI1504-LSSAX



CI3004-LSSAX-1



CI3004-LSSX-1



CISSX-6



Cat. No.	Volume (Cu. in.)	Features	Knockouts			Pryouts
		Clamps	1/2 in. ends	1/2 in. bottom	3/4 in. ends	ends
Device Boxes — 2-1/2 in. Deep — Gangable — 3 in. x 2 in.						
CI3104-KSSX	16.0	-	2	2	2	-
BC3104-KSS1X-1	16.0	-	2	2	2	-
BC3104-LSSAX	16.0	loomex/BX	-	-	-	4
BC3104-LSSX	16.0	loomex/BX	-	-	-	4
CI3104-LSS1X-1	16.0	loomex/BX	-	-	-	4
CI3104-LSSA1X-1	16.0	loomex/BX	-	-	-	4
CI3104-SSX	16.0	loomex/BX	2	2	-	-
Device Boxes — 2-1/2 in. Deep — Non-Gangable — 3 in. x 2 in.						
CI1504-LSSAX	15.0	loomex/BX	-	-	-	4
Device Boxes — 3 in. Deep — Gangable — 3 in. x 2 in.						
CI3004-LSSAX-1	18.0	loomex/BX	-	-	-	4
CI3004-LSSX	18.0	loomex/BX	-	-	-	4
CI3004-LSSX-1	18.0	loomex/BX	-	-	-	4

Cat. No.	Description
Support Brackets	
CISSX-6	Support bracket extension for 6 in. metal stud