

Tool Sets

41-Piece Journeyman™ Tool Set

JOURNEYMAN

- Comfortable and durable tools for the professional.



80141

Cat. No.	Set Contains	Weight (lbs.)
80141		29.8

Cat. No.	Description
BLK12	12-piece ball-end hex-key caddy set – inch
J203-6	Journeyman™ standard long-nose pliers
J203-8N	Journeyman™ heavy-duty long-nose pliers – side-cutting & stripping
J502-10	10" Journeyman™ pump pliers with 1-3/4" (44 mm) jaw capacity
D507-8	8" adjustable wrench – extra capacity
D507-12	12" adjustable wrench – extra capacity
600-1	1/4" keystone-tip cushion-grip screwdriver – 1-1/2" (40 mm) round-shank
600-4	1/4" keystone-tip cushion-grip screwdriver – 4" (102 mm) heavy-duty square-shank
601-3	3/16" cabinet-tip cushion-grip screwdriver – 3" (76 mm) round-shank
601-6	3/16" cabinet-tip cushion-grip screwdriver – 6" (152 mm) round-shank
602-6	5/16" keystone-tip cushion-grip screwdriver – 6" (152 mm) heavy-duty round-shank
603-1	No. 2 Phillips cushion-grip screwdriver – 1-1/2" (40 mm) round-shank
603-3	No. 1 Phillips cushion-grip screwdriver – 3" (76 mm) round-shank
603-4B	wire bending No. 2 Phillips cushion-grip screwdriver – 4" (102 mm) round-shank

Cat. No.	Description
605-6	1/4" cabinet-tip cushion-grip screwdriver – 6" (152 mm) heavy-duty round-shank
631	7-piece cushion-grip nut driver set (3/16", 1/4", 5/16", 11/32", 3/8", 7/16", 1/2")
650	cushion-grip scratch awl
662	No. 2 square-recess tip cushion-grip screwdriver – 4" (102 mm) round-shank
670-6	3/16" cabinet-tip cushion-grip screwdriver – Rapi-Driv®
916-25RE	25' x 1" power-return rule – magnetic tip
931-9RE	torpedo level - magnetic
J1005	Journeyman™ crimping/cutting tool – non-insulated and insulated connectors
K1412	Klein-Kurve® dual NM cable stripper/cutter
J2000-9NETP	Journeyman™ high-leverage side-cutting pliers – fish tape pulling
J2000-48	Journeyman™ high-leverage diagonal-cutting pliers – angled head
5003-18	18" 10-pocket canvas tool bag with leather bottom
5139	canvas zipper bag
11055	Klein-Kurve® wire stripper/cutter – 10-18 AWG solid & 12-20 AWG stranded
44107	Klein-Kurve® heavy-duty utility knife – quick change retractable blade
46037	cable-splicer's kit
50211	120' Speedway® flat-steel fish tape – Grip-It® handle
58889	padded adjustable shoulder strap
60053	standard protective eyewear
J63050	Journeyman™ high-leverage cable cutter
85191	conduit-fitting and reaming screwdriver

All dimensions are in inches and (millimeters) unless otherwise specified.

▲WARNING: Always wear approved eye protection.

▲WARNING: NOT insulated. Do NOT use these tools on or near live electrical circuits.

▲WARNING: Do NOT use screwdrivers to pry or chisel.

▲WARNING: Do NOT open the tape measure case. Spring motor is under tension, and opening may cause injury.

▲WARNING: When working with fish tape, always use safe work position to avoid loss of balance.

▲WARNING: Never remove screws while fish tape is coiled inside reel.

