



Fire Barrier CP 25WB+ Caulk



Sizes to meet all your needs

Get the most versatile firestop caulk on the market. Firestop provides a wide variety of typical pipe and cable penetrations through fire-rated construction. Its versatility simplifies your firestopping needs. 3M™ Fire Barrier CP 25WB+ caulk is a premium elastomeric latex designed for use as a one-part fire,

smoke, noxious gas and water sealant. Its unique property allows CP 25WB+ caulk to effectively contain fire and smoke at its origin.

Available in a variety of sizes, CP 25WB+ caulk can be installed with a standard caulking gun, pneumatic pumping equipment or a putty knife or trowel.

3M™ Fire Barrier CP 25WB+ Caulk

10.1-oz. tube



Lightweight, easy to handle. Perfect for smaller jobs. 12 tubes per box.

20-oz. sausage



Less mess. Less waste. Eliminates empty cartridges from the job site. Versatile application gun can be used with other guns including pneumatics. 10 sausages per box.

27-oz. tube



Don't mess with bulk loading. Spend less time reloading tubes on bigger jobs. 6 tubes per box.

2-gallon pail



Lighter and easier to carry around job site. Applies easily with a putty knife or trowel.

5-gallon pail



Great for bulk loading on large jobs. The most cost-effective way to caulk large areas.

Product Features

- Water based for easy cleanup and routine disposal with no special handling
- One-part system—no mixing or measuring
- Intumescent and endothermic properties
- No-sag, non-halogen formula
- Fast drying in just 10-15 minutes
- Paintable
- Documented aging properties

Warranty and Limited Remedy. This product will be free from defects in material and manufacture for a period of ninety (90) days from date of purchase. **3M MAKES NO OTHER WARRANTIES INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE.** User is responsible for determining whether the 3M product is fit for a particular purpose and suitable for user's application. If the 3M product is proved to be defective within the warranty period stated above, your exclusive remedy and 3M's sole obligation shall be, at 3M's option, to replace or repair the 3M product or refund the purchase price of the 3M product.

Limitation of Liability. Except where prohibited by law, 3M will not be liable for any loss or damage arising from a 3M product, whether direct, indirect, special, incidental or consequential, regardless of the legal theory asserted, including warranty, contract, negligence or strict liability.



3M Consumer Safety and Light Management

3M Center, Building 223-2N-21
St. Paul, MN 55144-1000
Phone: 800-328-1687
www.3M.com/firestop



40% Pre-consumer waste paper
10% Post-consumer waste paper

Printed in U.S.A.

Copyright © 2002, 3M IPC.
All rights reserved.

98-0400-4976-3 (1121.3)ii

3M Innovation