

Straight blade power devices 20, 30, 50 & 60A



Rating: Amps V/AC	Receptacle/ plug NEMA configuration	Flush receptacles	Wallplate	Surface receptacle	Panel mount receptacle	Plugs	Angle plugs
-------------------------	-------------------------------------------	----------------------	-----------	-----------------------	---------------------------	-------	-------------

3-pole, 4-wire grounding

20A 125/250V	 14-20R	 14-20P	Industrial: 5759 (Black)				
30A 125/250V Dryer	 14-30R	 14-30P	Commercial: 1257 (Black)	Standard size: 39CH, 68, 2068, 2168, 93221, 93227	Commercial: 1225 (Black)	Industrial: 5746N (Gray)	Commercial: S21 (Black)
			Industrial: 5744N (Black)	Mid-size: 5068, PJ703, PJ724			Standard size: 69, 5169, 93223
30A 3Ø 250V	 15-30R	 15-30P	Industrial: 8430N (Black)	Standard size: 69, 5169, 93223		Industrial: 8432N (Gray)	Industrial: 8432AN (Gray)
50A 125/250V Range	 14-50R	 14-50P	Commercial: 1258 (Black)	Standard size: 39CH, 68, 2068, 2168, 93221, 93227	Commercial: 1212 (Black)	Commercial: 58 (Black)	Commercial: S21 (Black)
			Industrial: 5754N (Black)	Mid-size: 5068, PJ703, PJ724			Standard size: 69, 5169, 93223
50A 3Ø 250V	 15-50R	 15-50P	Industrial: 8450N (Black)	Standard size: 69, 5169, 93223		Industrial: 8450P (Black)	Industrial: 8452N (Gray)
60A 125/250V	 14-60R	 14-60P	Industrial: 9460N (Black)	Standard size: 69, 5169, 93223		Commercial: 60 (Black)	Commercial: S20 (Black)
						Industrial: 9462N (Gray)	Industrial: 9462AN (Gray)
60A 3Ø 250V	 15-60R	 15-60P	Industrial: 8460N (Black)	Standard size: 69, 5169, 93223		Industrial: AH8462N (Gray)	Industrial: AH8462AN (Gray)

4-pole, 4-wire, non-grounding

30A 3ØY 120/208V	 18-30R	 18-30P				Industrial: 8332N (Gray)	Industrial: 8332AN (Gray)
50A 3ØY 120/208V	 18-50R	 18-50P				Industrial: 8352N (Gray)	Industrial: 8352AN (Gray)
60A 3ØY 120/208V	 18-60R	 18-60P	Industrial: 5515N (Black)	Standard size: 69, 5169, 93223		Industrial: 5517N (Gray)	Commercial: S19 (Black)
						Industrial: 4516AN (Gray)	

Power device dimensional information: B-20; Specification information: B-25-B-27
Compliances, specifications and availability are subject to change without notice.

All products on this page are RoHS compliant – Page Q-30