



# STRAIGHT BLADE RECEPTACLES

## Commercial Specification Grade Receptacles Tamper-Resistant 15 & 20A, 125V



**TR26242I**

**TR26352GRY**

### Features

- Dual mechanical shutter system to help prevent insertion of foreign objects.
- Impact-resistant nylon face for durability.
- .032-inch thick brass triple-wipe power contacts for reliable plug retention.
- Auto-ground clip assures positive ground.
- Corrosion-resistant, plated steel strap.
- Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.
- Backed-out tri-drive steel terminal screws for faster installation.

CATALOG NUMBER	RATING		COLOR	NEMA CONFIG. NO.	3rd PARTY COMPLIANCE	
	A.	V.			UL498	C22.2 No. 42
<b>DUPLEX RECEPTACLES SIDE WIRE</b>						
TR26242I	15	125	Ivory	5-15R	•	•
TR26242W	15	125	White	5-15R	•	•
TR26242	15	125	Brown	5-15R	•	•
TR26242GRY	15	125	Gray	5-15R	•	•
TR26242BK	15	125	Black	5-15R	•	•
TR26242RED	15	125	Red	5-15R	•	•
TR26242LA	15	125	Light Almond	5-15R	•	•
TR26342I	20	125	Ivory	5-20R	•	•
TR26342W	20	125	White	5-20R	•	•
TR26342	20	125	Brown	5-20R	•	•
TR26342GRY	20	125	Gray	5-20R	•	•
TR26342BK	20	125	Black	5-20R	•	•
TR26342RED	20	125	Red	5-20R	•	•
TR26342LA	20	125	Light Almond	5-20R	•	•
<b>DUPLEX RECEPTACLES BACK &amp; SIDE WIRE</b>						
TR26252I	15	125	Ivory	5-15R	•	•
TR26252W	15	125	White	5-15R	•	•
TR26252	15	125	Brown	5-15R	•	•
TR26252GRY	15	125	Gray	5-15R	•	•
TR26252BK	15	125	Black	5-15R	•	•
TR26252RED	15	125	Red	5-15R	•	•
TR26252LA	15	125	Light Almond	5-15R	•	•
TR26352I	20	125	Ivory	5-20R	•	•
TR26352W	20	125	White	5-20R	•	•
TR26352	20	125	Brown	5-20R	•	•
TR26352GRY	20	125	Gray	5-20R	•	•
TR26352BK	20	125	Black	5-20R	•	•
TR26352RED	20	125	Red	5-20R	•	•
TR26352LA	20	125	Light Almond	5-20R	•	•

### 2 Pole, 3 Wire



For Bulk Packaging Solutions consult factory.

All devices listed on this page conform to NEMA WD-1 and WD-6.

# DEVICES & WALL PLATES

## Color Selection Chart

### Devices & Plastic Wall Plate Colors



Ivory    Light Almond    White    Green    Antique Brass    Dark Bronze    Nickel



Black    Blue    Brown    Gray    Orange    Red

See specific device and wall plate catalog charts for particular color availabilities.

### Metal Wall Plates

Metal Finish



Aluminum    Brass (Brushed)    Polished Brass    Stainless Steel    Brushed Bronze    Chrome

### Custom Metal Wall Plates Paint Finish Colors

Paint Color



Orange    Green    Gray    Yellow    Glossy Black    Brown    White



Primer    Red    Pink    Flat Black    Ivory    Light Almond    Blue

To order custom metal wall plates, see Pages P-40 – P-44.

**For additional colors consult factory.**