



Selection and ordering data

Octal Base (Standard)

Contacts	Contact Rating (A)	Coil Voltage	Basic Relay	Premium Relay	Premium Bifurcated	Uses Socket 3TX7144-	Uses Clip 3TX7144-	Socket Access Set	Panel Mount Adaptor 3TX7144-	DIN Rail Mount Adaptor 3TX7144-
DPDT	16	12 VDC	3TX7112-1DB03C	3TX7112-1LB03	—	3TX7144-4E2	1L14	A	—	—
		12 VAC	3TX7112-1DB13C	3TX7112-1LB13	—	3TX7144-4E2	1L14	A	—	—
		24VDC	3TX7112-1DC03C	3TX7112-1LC03	—	3TX7144-4E2	1L14	A	—	—
		24VAC	3TX7112-1DC13C	3TX7112-1LC13	—	3TX7144-4E2	1L14	A	—	—
		110 VDC	3TX7112-1DF03C	3TX7112-1LF03	—	3TX7144-4E2	1L14	A	—	—
		120 VAC	3TX7112-1DF13C	3TX7112-1LF13	—	3TX7144-4E2	1L14	A	—	—
		220/230 VAC	3TX7112-1DG13C	3TX7112-1LG13	—	3TX7144-4E2	1L14	A	—	—
3PDT	16	12 VDC	3TX7112-1FB03C	3TX7112-1NB03	—	3TX7144-4E3	1L14	A	—	—
		12 VAC	3TX7112-1FB13C	3TX7112-1NB13	—	3TX7144-4E3	1L14	A	—	—
		24VDC	3TX7112-1FC03C	3TX7112-1NC03	—	3TX7144-4E3	1L14	A	—	—
		24VAC	3TX7112-1FC13C	3TX7112-1NC13	—	3TX7144-4E3	1L14	A	—	—
		110 VDC	3TX7112-1FF03C	3TX7112-1NF03	—	3TX7144-4E3	1L14	A	—	—
		120 VAC	3TX7112-1FF13C	3TX7112-1NF13	—	3TX7144-4E3	1L14	A	—	—
		220/230 VAC	3TX7112-1FG13C	3TX7112-1NG13	—	3TX7144-4E3	1L14	A	—	—



Hermetically Sealed (Class 1 Div 2)

Contacts	Contact Rating (A)	Coil Voltage	Basic Relay	Premium Relay	Premium Bifurcated	Uses Socket 3TX7144-	Uses Clip 3TX7144-	Socket Access Set	Panel Mount Adaptor 3TX7144-	DIN Rail Mount Adaptor 3TX7144-
(Octal) DPDT	12	12 VDC	3TX7127-5HB00	—	—	3TX7144-4E2	1L12	A	—	—
		24 VDC	3TX7127-5HC00	—	—	3TX7144-4E2	1L12	A	—	—
		24 VAC	3TX7127-5HC10	—	—	3TX7144-4E2	1L12	A	—	—
		110 VDC	3TX7127-5HF00	—	—	3TX7144-4E2	1L12	A	—	—
		120 VAC	3TX7127-5HF10	—	—	3TX7144-4E2	1L12	A	—	—
		240 VAC	3TX7127-5HG13	—	—	3TX7144-4E2	1L12	A	—	—
(Octal) 3PDT	12	12 VDC	3TX7127-7HB00	—	—	3TX7144-4E3	1L12	A	—	—
		24 VDC	3TX7127-7HC00	—	—	3TX7144-4E3	1L12	A	—	—
		24 VAC	3TX7127-7HC10	—	—	3TX7144-4E3	1L12	A	—	—
		110 VDC	3TX7127-7HF00	—	—	3TX7144-4E3	1L12	A	—	—
		120 VAC	3TX7127-7HF10	—	—	3TX7144-4E3	1L12	A	—	—
		240 VAC	3TX7127-7HG13	—	—	3TX7144-4E3	1L12	A	—	—
(Square) 4PDT	3	12 VDC	3TX7127-3HB00	—	—	3TX7144-4E5	1L11	B	—	—
		24VDC	3TX7127-3HC00	—	—	3TX7144-4E5	1L11	B	—	—
		24VAC	3TX7127-3HC10	—	—	3TX7144-4E5	1L11	B	—	—
		110 VDC	3TX7127-3HF00	—	—	3TX7144-4E5	1L11	B	—	—
		120 VAC	3TX7127-3HF10	—	—	3TX7144-4E5	1L11	B	—	—
(Square) 4PDT	5	12 VDC	3TX7127-3HB03	—	—	3TX7144-4E5	1L11	B	—	—
		24VDC	3TX7127-3HC03	—	—	3TX7144-4E5	1L11	B	—	—
		120 VAC	3TX7127-3HF13	—	—	3TX7144-4E5	1L11	B	—	—
		230 VAC	3TX7127-3HG13	—	—	3TX7144-4E5	1L11	B	—	—

Option	Basic	Premium	Premium Bifurcated
Mechanical Flag	✓	✓	✓
Push To Test		✓	✓
Lock Down Door		✓	✓
LED		✓	✓

Note: See page 11/84 for socket accessories.