## FLEXCOR® WIRE MESH GRIPS

## Support Grips Service & Bus Drop





Service Drop Closed Mesh Single Eye

Service Drop Closed Mesh Locking Bale



Bus Drop Closed Mesh Single Eye



Bus Drop Closed Mesh Locking Bale



**Bus Drop Accessories** 

## **Description**

Service drop grips provide support for utility distribution lines from service pole to building or from pole to pole. They can also be used for cable TV and fiber optic cable support. They are woven from tinned bronze wire to provide superior corrosion resistance, and are available in single eye and locking bale configurations.

CATALOG NUMBER	CABLE DIAMETER RANGE	BALE LENGTH	MESH LENGTH	APPROXIMATE BREAK STRENGTH*				
SERVICE DROP, CLOSED MESH, SINGLE EYE								
FCSD22	0.220"-0.320"	4"	4"	290 lbs.				
FCSD30	0.300"-0.430"	5"	5"	500 lbs.				
FCSD40	0.410"-0.560"	6"	5"	500 lbs.				
FCSD52	0.530"-0.730"	8"	8"	790 lbs.				
FCSD70	0.700"-0.970"	8"	9"	1,020 lbs.				
FCSD94	0.940"-1.250"	10"	11"	1,020 lbs.				
SERVICE DROP, CLOSED MESH, LOCKING BALE								
FCSD30LB	0.300"-0.430"	11"	5"	500 lbs.				
FCSD52LB	0.530"-0.730"	14"	8"	790 lbs.				
FCSD70LB	0.700"-0.970"	14"	9"	1,020 lbs.				
FCSD94LB	0.940"-1.250"	16"	11"	1,020 lbs.				

\*To determine workload safety factor, divide approximate break strength by 10.

See Page J-23 for strength information.

## **Description**

Bus drop grips are used as cable support. They relieve any direct tension from the critical connection and absorb vibration and flexing. Bus drop grips are woven of galvanized steel wire. They are offered with either the single eye or locking bale attachment.

CATALOG NUMBER	CABLE DIAMETER RANGE	BALE LENGTH	MESH LENGTH	APPROXIMATE BREAK STRENGTH*	CATALOG NUMBER	NPT SIZE	
BUS DROP, CLOSED MESH, SINGLE EYE						BUS DROP ACCESSORIES	
FC22	0.220"-0.320"	9"	3.5"	1,100 lbs.	S40	Safety Spring, 40 Lb. Load	
FC30	0.300"-0.430"	9"	4.5"	1,100 lbs.	S80	Safety Spring, 80 Lb. Load	
FC40	0.410"-0.560"	9"	5.0"	1,100 lbs.		5 1 5.	
FC52	0.530"-0.730"	9"	6.5"	1,100 lbs.	GH5	Support Hook	
FC70	0.700"-0.850"	9"	8.5"	1,900 lbs.			
FC94	0.940"-1.250"	9"	11.0"	1,900 lbs.			
BUS DROP, CLOSED MESH, LOCKING BALE							
FC30LB	0.300"-0.430"	12"	4.5"	1,100 lbs.			
FC40LB	0.410"-0.560"	12"	5.0"	1,100 lbs.			
FC52LB	0.530"-0.730"	15"	6.5"	1,100 lbs.			
FC70LB	0.700"-0.850"	16"	8.5"	1,900 lbs.			
FC94LB	0.940"-1.250"	17"	11.0"	1.900 lbs.			

\*To determine workload safety factor, divide approximate break strength by 10. See Page J-23 for strength information.