


Beams, Purlin and Hangers

Beam Clamps

Features



- Fits beam flanges to 1/2 in.
- Supports 1/4 in. and 3/8 in. threaded rod, s-hooks, electrical boxes, conduit and bridle rings
- 1/4 in.-20 or #10-24 threaded openings




Fig. 1




Fig. 2




Fig. 3

Features

- Fits beam flanges to 1/2 in.
- Supports 1/4 in. and 3/8 in. threaded rod, s-hooks, electrical boxes, conduit and bridle rings
- 1/4 in.-20 or #10-24 threaded openings




Fig. 4




Fig. 5



Cat. No.	Fig. No.	Description	Static Load Limit	Qty. Per Box
Beam Clamps				
SSF-BBC	1	Stamped steel beam clamp	100	100
SSF-BBC-S1/2V*	2	Beam clamp thru 1/2 in. flange to conduit clamp, 1/2 in. conduit	25	25
SSF-BBC-S3/4V*	2	Beam clamp thru 1/2 in. flange to conduit clamp, 3/4 in. conduit	25	25
SSF-BBC-S1V*	2	Beam clamp thru 1/2 in. flange to conduit clamp, 1 in. conduit	25	25
SSF-BBC-S1/2H*	3	Beam clamp thru 1/2 in. flange to side mounted conduit clamp, 1/2 in. conduit	15	25
SSF-BBC-S3/4H*	3	Beam clamp thru 1/2 in. flange to side mounted conduit clamp, 3/4 in. conduit	15	25
SSF-BBC-S1H*	3	Beam clamp thru 1/2 in. flange to side mounted conduit clamp, 1 in. conduit	15	25

* UL/cUL not applicable

Cat. No.	Fig. No.	Description	Static Load Limit	Qty. Per Box
Beam Clamps				
SSF-BBC-C1/2 3/4V	4	Beam clamp thru 1/2 in. flange to conduit clamp, 1/2 in.-3/4 in. conduit	100	25
SSF-BBC-C1V	4	Beam clamp thru 1/2 in. flange to conduit clamp, 1 in. conduit	100	
SSF-BBC-C1 1/4V	4	Beam clamp thru 1/2 in. flange to conduit clamp, 1-1/4 in. conduit	100	
SSF-BBC-C1 1/2V	4	Beam clamp thru 1/2 in. flange to conduit clamp, 1-1/2 in. conduit	100	
SSF-BBC-C2V	4	Beam clamp thru 1/2 in. flange to conduit clamp, 2 in. conduit	100	
SSF-BBC-C1/2 3/4H	5	Beam clamp thru 1/2 in. flange to side mounted conduit clamp, 1/2 in.-3/4 in. conduit	25	
SSF-BBC-C1H	5	Beam clamp thru 1/2 in. flange to side mounted conduit clamp, 1 in. conduit	25	
SSF-BBC-C1 1/4H	5	Beam clamp thru 1/2 in. flange to side mounted conduit clamp, 1-1/4 in. conduit	25	
SSF-BBC-C1 1/2H	5	Beam clamp thru 1/2 in. flange to side mounted conduit clamp, 1-1/2 in. conduit	25	
SSF-BBC-C2H	5	Beam clamp thru 1/2 in. flange to side mounted conduit clamp, 2 in. conduit	25	