



TRAC-LITES

Line and Low Voltage

MONOPOINTS and SPECIAL MOUNTINGS

Project: _____

Fixture Type: _____


Location: _____

Contact/Phone: _____


PRODUCT DESCRIPTION

Special adapters permit the flexibility of mounting trac lights in various ways to meet special requirements.


Line Voltage Monopoint Adapters




R40N-WH, R40N-BL, R40N-SL, R40N-BZ
Monopoint Adapter. Mounts directly to outlet box. Accepts one 120V Juno trac fixture.




T40F-WH, T40F-BL, T40F-SL
Flush Monopoint Adapter. Mounts directly to outlet box. Accepts one 120V Juno trac fixture with standard size trac adapter.




T41N-WH, T41N-BL, T41N-SL
Duo-Point Adapter. Mounts directly to an outlet box. Accepts two 120V Juno trac fixtures.




T42N-WH, T42N-BL
Weighted Base. For portable use. Supplied with 8' cord and plug. Accepts one 120V Juno trac fixture.



T46
Clamp/Monopoint Adapter. Clamps to pipe or planking up to 2 1/2" thick. Accepts 120V Juno trac fixture with standard size trac adapter. Supplied with 8' three-wire cord and plug.




T45WH, T45BL
Pin-Up/Monopoint Adapter. Supplied with 8' cord and plug. Accepts one 120V Juno trac fixture with standard size trac adapter.



T57N-WH
Monopoint Line Voltage Cover. Attaches one 120V trac fixture directly to Juno's 6" recessed universal housings.

Line Voltage Coil - Cord Clamp-Ons



T132WH, T132BL
120V Monopoint with trac adapter for electrical connection to Trac. Accepts one 120V Juno trac fixture with standard size trac adapter. 2' Coil Cord extends to 5'. 1-3/4" Clamp opening.

T133WH, T133BL
120V Monopoint with male plug (120V) attaches to receptacle. Accepts one 120V Juno trac fixture with standard size trac adapter. 2' Coil Cord extends to 5'. 1-3/4" Clamp opening.


Line Voltage Extension Wands



TW12, TW18, TW24, TW36, TW48
Line Voltage Extension Wands (12", 18", 24", 36", 48") - For use with one or two circuit trac and line voltage monopoints. Accepts one 120V Juno trac fixture with standard size trac adapter. WH, BL, SL


TWS24WH, TWS24BL, TWS24SL
24" Wand with Slope Adapter. Accepts one 120V Juno trac fixture with standard size trac adapter.

Line Voltage Sloped Ceiling Adapter



T95WH, T95BL, T95SL, T95BZ
Sloped Ceiling Adapter. Attaches to trac, permitting Trac-Master or Trac-Lites Trac fixtures with standard size trac adapter to be hung vertically from sloped ceiling. 90° maximum adjustable.

Low Voltage Monopoint Adapter



R58WH, R58BL, R58SL
Monopoint Adapter for T537, T538 or Trac-Lites R Series Low-Voltage Power Packs. Mounts directly to outlet box. Adapter is offset to accept all Power Pack styles. Power Pack latch locks in detent.

Product specifications subject to change without notice.

