

Premium Crimping Tool

NEW

K210



- Storage for two sets of crimping dies in the handles.
- No tools needed to change dies.
- Precision machined for smooth crimping cycles.
- Hardened mechanism components for long term durability.
- Cushioned handles for comfort.
- Full cycle mechanism assures complete crimps, but tool can be opened in mid-cycle if necessary.
- Equipped with 3 crimping die sets for 22-10 AWG insulated terminals (red, yellow, blue), 22-10 AWG uninsulated terminals, and 26-8 AWG wire ferrules.

CAT. NO.	UPC NO.	DESCRIPTION
K210	10872	Crimping Tool with 10873, 10874 & 10875 die sets
10873	10873 R	Die set, 22-10 AWG Insulated Terminals
10874	10874 R	Die set, 22-10 AWG Uninsulated Terminals
10875	10875 R	Die set, 26-8 AWG Wire Ferrules
10876	10876 R	Die set, RG, 58/59/62/71
10877	10877 R	Die set, 20-10 AWG Barrel Connectors

SPECIFICATIONS

Overall Length	9" (23 cm)
Weight	1.35 lbs. (.6 kg)
Insulated Terminals & Splices	22-10 AWG
Uninsulated Terminals & Splices	22-10 AWG
Wire Ferrules	26-8 AWG

Crimping/Stripping Combination Tool

KP1022



KP1022D

- Two die positions permit the KP1022 to crimp both insulated and uninsulated terminals and splices.
- Forged steel and hardened design provides long life.
- Smooth pivot action allows tool to easily be used with one hand.
- Double-cushioned handle grips are easy on the hands.
- Precision machined and hardened cutter blades make wire cutting easy.

CAT. NO. UPC NO. DESCRIPTION

KP1022	02155	Terminal Crimping Tool with molded grip
KP1022D	10633 N	Terminal Crimping Tool with dipped grip

SPECIFICATIONS

Overall Length	9-1/2" (241 mm)
Weight	1.05 lbs. (.48 kg)
Insulated Terminals & Splices	10-22 AWG
Uninsulated Terminals & Splices	10-22 AWG

SCREW & NUT DRIVERS

5-Piece Screwdriver Set



0153-01C

- Heavy-duty construction for longer life.
- Handle marked for easy identification of screwdriver size, type and length.
- Precision-machined tips for accurate fastener contact.
- Strong, durable black phosphate tips prevent chipping of plating.
- High-grade, rust resistant, chrome-plated finish.
- Soft, cushioned grip for extra comfort and torque.
- Exceeds ASME/ANSI specifications.
- Lifetime limited warranty.
- Note: This is not an insulated tool.

CAT. NO. UPC NO. DESCRIPTION

0153-01C	56303	5-Piece Screwdriver Set
0153-01C-CP	95930	5-Piece Screwdriver Set Counter Pack (Qty 5)

SPECIFICATIONS

Contains	3/16" x 6" Cabinet, 1/4" x 4" Keystone, 1/4" x 6" Cabinet, 5/16" x 6" Keystone & #2 x 4" Phillips
Weight	1.38 lbs. (.63 kg)