## **MASONRY BITS** Quick Change Carbide Tipped Masonry Bits



 One piece hardened carbon steel body and hex shank for a stronger, more concentric bit that will not disassemble when drilling in deep or tough materials.

**GREENLEE** 

- Carbide grade tip for faster penetration and longer bit life.
- Hammer drill rated for use in either standard or hammer drills.
- 1/4" quick-change hex for fast bit changes. Use in quick-change chucks, conventional adjustable drill chucks, and hex adapters for more versatility.
- Set includes diameters and lengths most commonly used by electricians.

SPECIFICATIONS			CAT. NO.	UPC NO.	DESCRIPTION 1/2" Masonry Drill Bit, (POP)
			MAS-1/2	04943	
	Dimensions	Weight	MAS-1/4	26322	1/4" Masonry Drill Bit (POP)
MAS-1/2	1.9" x 6.3" x .5"	0.2	MAS-1/8	02162	1/8" Masonry Drill Bit (POP)
MAS-1/4	1.9" x 6.3" x .25"	0.1	MAS-3/16	26315	3/16" Masonry Drill Bit (POP)
MAS-1/8	1.9" x 11.6" x .13"	0.1	MAS-3/8	19202	3/8" Masonry Drill Bit (POP)
MAS-3/16	1.9" x 6.3" x .2"	0.1	MAS-5/16	04942	5/16" Masonry Drill Bit (POP)
MAS-3/8	1.9" x 6.3" x .38"	0.2	MAS-5/32	04941	5/32" Masonry Drill Bit (POP)
MAS-5/16	1.9" x 6.3" x .32"	0.2	MAS-SET	26318	Masonry Drill Set (POP)
MAS-5/32	1.9" x 6.3" x .16"	0.1	MINO OLI	20010	Includes: (1) 1/4", (1) 3/16", (1) 3/8", (1) 5/32"
MAS-SET	7.5" x 5.5" x .5"	0.3	MAS-SET-9	02145	Hex Quick Change Masonry Bit Kit (POP)
MAS-SET-9	7.9" x 5.4" x 1"	0.8			Includes: (1) 1/2", (2) 1/4", (2) 3/16", (1) 3/8", (1) 5/16", (2) 5/32"

## **SDS-PLUS Carbide Tipped Masonry Bits**



## Hardened, premium carbide insert tip is strong and stays sharp longer for finer material break up and easier drilling.

- Shaft made from hardened alloy steel for heavy shock resistance and longer bit life.
- Carbide tip sized in inches versus mm for more accurate hole size.
- H-Style flute for faster drilling and material removal
- SDS Plus drive for more secure hold in rotary hammer drill.
- Kit includes diameters and lengths most commonly used by electricians.

	Dimensions	Weight			
SDS-1/2	1.9" x 9.3" x .5"	0.3			
SDS-1/4	1.9" x 9.3" x .25"	0.1			
SDS-3/16	1.9" x 9.3" x .2"	0.1			
SDS-3/4	1.9" x 11.6" x .8"	0.6			
SDS-3/8	1.9" x 9.3" x .38"	0.3			
SDS-5/8	1.9" x 9.3" x .63"	0.6			
SDS-SET-5	7.3" x 9.9" x 1"	1.6			

CAT. NO.	UPC NO.	DESCRIPTION
SDS-1/2	04947	1/2" SDS-Plus Masonry Bit 6" (POP)
SDS-1/4	04945	1/4" SDS-Plus Masonry Bit, 6" (POP)
SDS-3/16	04944	3/16" SDS-Plus Masonry Bit, 6" (POP)
SDS-3/4	02163	3/4" SDS-Plus Masonry Bit, 8- 1/4" (POP)
SDS-3/8	04946	3/8" SDS-Plus Masonry Bit, 6" (POP)
SDS-5/8	04948	5/8" SDS-Plus Masonry Bit, 6" (POP)
SDS-SET-5	02154	SDS-Plus Masonry Bit Kit (POP)
		Includes: (1) 3/16", (1) 1/4", (1) 3/8", (1) 1/2", (1) 5/8"