

Electrician's Straight-Claw Hammer



- Durable plastic-alloy jacketing helps to protect neck from fraying and splintering if incorrectly struck or overstruck.
- High-strength fiberglass shaft absorbs shock and keeps head tight.
- Comfortable, perforated neoprene grip bonded to handle.
- Correctly balanced and designed specifically for use in electrical work.
- Extra-long neck, and narrow striking face are ideal for reaching into outlet boxes and other tight areas.

Cat. No.	Head Weight	Overall Length	Weight (lbs.)
807-18	18 oz. (510 g)	15" (381 mm)	1.85

Curved-Claw Hammers – Heavy-Duty



- Durable plastic-alloy jacketing helps to protect neck from fraying and splintering if incorrectly struck or overstruck.
- High-strength fiberglass shaft absorbs shock and keeps head tight.
- Comfortable, perforated neoprene grip bonded to handle.
- Curved claw gives maximum nail-pulling leverage.

Cat. No.	Head Weight	Overall Length	Weight (lbs.)
818-16	16 oz. (454 g)	13" (330 mm)	1.85
818-20	20 oz. (567 g)	14" (356 mm)	2.00

Lineman's Straight-Claw Hammer



- Heavy-duty, double-duty hammer drives lags and pulls big nails.
- Special high-carbon steel head with solid, octagon-shaped driving end and thick, strong claw.
- Straight-grain hickory handle, lacquered.

Cat. No.	Head Weight	Overall Length	Weight (lbs.)
832-32	32 oz. (907 g)	15" (381 mm)	2.50

Straight-Claw Hammers – Heavy-Duty



- Durable plastic-alloy jacketing helps to protect neck from fraying and splintering if incorrectly struck or overstruck.
- High-strength fiberglass shaft absorbs shock and keeps head tight.
- Comfortable, perforated neoprene grip bonded to handle.
- Straight-claw design for easy nail pulling in tight quarters.

Cat. No.	Head Weight	Overall Length	Weight (lbs.)
808-16	16 oz. (454 g)	13" (330 mm)	1.85
808-20	20 oz. (567 g)	14" (356 mm)	2.00

Ball-Peen Hammers



- High-carbon steel head is forged and hardened.
- Crowned face with uniform bevel.
- Smoothly rounded peen.
- Straight-grain hickory handle is stained and lacquered.

Cat. No.	Head Weight	Overall Length	Weight (lbs.)
803-8	8 oz. (227 g)	11-1/2" (292 mm)	.75
803-12	12 oz. (340 g)	12-1/2" (318 mm)	1.10
803-16	16 oz. (454 g)	13-1/2" (343 mm)	1.40
803-24	24 oz. (680 g)	15" (381 mm)	1.90
803-32	32 oz. (907 g)	15" (381 mm)	2.50

Lineman's Double-Face Hammer



- Designed for pole-line work.
- Rugged and well-balanced, with the weight to drive lag bolts.
- Forged, tempered-steel head is only 3-3/4" (95 mm) long for use in tight areas.
- Identical faces with 1-3/4" (44 mm) round-crown driving surface and beveled edges.

Cat. No.	Head Weight	Overall Length	Weight (lbs.)
809-36	36 oz. (1021 g)	14" (356 mm)	2.50

