







SPECIFICATIONS

	/ I&F
Maximum Capacity*	
Copper:	350 kcmil (MCM) (150 mm²)
Aluminum:	-
Communications Cable:	1" (25 mm) dia.
Frequent Use Capacity*	
Copper:	4/0 AWG (95))
Aluminum:	350 kcmil (MCM) (150 mm²)

 Communications Cable:

 Length
 17-1/2" (444 mm)

 Weight:
 2.8 lbs. (1.3 kg)

718F, 704, 705 and 706

- Strong, lightweight fiberglass handles.
- · Adjustable pivot bolt provides for blade adjustment.

704, 705 and 706

- Replaceable, forged, heat-treated, and precision ground blades.
- · Made in USA.

704	705	

350 kcmil (MCM) (150 mm²)	500 kcmil (MCM) (240 mm²)	750 kcmil (MCM) (400 mm²)
500 kcmil (MCM) (240 mm²)	1000 kcmil (MCM) (500 mm²)	1000 kcmil (MCM) (500 mm²)
1-1/4" (32 mm) dia.	1-3/4" (44 mm) dia.	1-1/2" (38 mm) dia.
250 kcmil (MCM) (120 mm²)	350 kcmil (MCM) (150 mm²)	500 kcmil (MCM) (240 mm²)
350 kcmil (MCM) (150 mm²)	750 kcmil (MCM) (400 mm²)	750 kcmil (MCM) (400 mm²)
-	-	-
21" (533 mm)	25-1/2" (648 mm)	31-1/2" (800 mm)

706

21" (533 mm)	25-1/2" (648 mm)	31-1/2" (800 mm)
3.01 lbs. (1.37 kg)	5.5 lbs. (2.5 kg)	6.2 lbs. (2.8 kg)

	CAT. NO.	UPC NO.	DESCRIPTION
	718F	10507	Heavy-Duty Cable Cutter, 17-1/2"
	704	24564	Heavy-Duty Cable Cutter, 21"
	705	05923	Heavy-Duty Cable Cutter, 25-1/2"
	706	22291	Heavy-Duty Cable Cutter, 31-1/2"
R	24565	24565	704 Cutter Unit (Includes 2 Blades)
R	24567	24567	704 Handle Unit (Includes Handle, Sleeve, Grip)
R	05930	05930	705 Handle Unit (Includes Handle, Sleeve, Grip)
R	06555	06555	705 & 706 Cutter Unit (Includes 2 Blades)
R	22296	22296	706 Handle Unit (Includes Handle, Sleeve, Grip)

*Capacity may be less for compact and compressed cables

718 Cable Cutter



- · Economical, lightweight, fits easily into tool boxes.
- · Heat-treated, precision ground, shear action blades.
- Steel handles with rubber grips for leverage.
- · Made in USA.

SPECIFICATIONS

	COPPER	ALUMINUM
Maximum Capacity*	350 kcmil (MCM) (150mm²)	-
Frequent Use Capacity	4/0 (95 mm²)	350 kcmil (MCM) (150 mm ²)
Length	18" (457 mm)	
Weight:	2.78 lbs. (1.3 kg)	
CAT NO LIDE NO	DESCRIPTION	

CAT. NO.	UPC NO.	DESCRIPTION
718	30208	Cable Cutter

*Capacity may be less for compact and compressed cables

718HL Cable Cutter



- Unique "double joint" reduces handle effort required by 25% and increases cutting capacity to 500 kcmil
- · Fits into tool boxes
- · Heat-treated, precision ground, shear action blades
- Strong steel handles with molded grips for good leverage
- · Patent Pending

SPECIFICATIONS

SPECIFICATIONS					
			COPPER	ALUMINUM	
Maximum Capacity*		Capacity*	500 kcmil	500 kcmil	
	Frequent Use Capacity		350 kcmil	500 kcmil)	
Length			18" (457 mm)		
	Weight:		3.25 lbs. (1.5 kg)		
	CAT. NO.	UPC NO.	DESCRIPTION		
	718HI	12847	Cable Cutter	·	

*Capacity may be less for compact and compressed cables