

RECESSED LIGHT HOLE SAWS

Recessed Light Hole Saws



- Industry's only interchangeable replacement blades.
- Strong durable back plate.
- Available in two styles – steel tooth and carbide grit.
- Use with a power drill to cut large diameter holes for recessed lighting fixtures.
- Saws use Greenlee arbor 37156, purchased separately.

SPECIFICATIONS

Capacity Steel Toothed Blade - up to 7/8" (22.2 mm) plywood, wood, acoustical tile and ceiling tile.
Carbide Grit Blade - up to 7/8" (22.2 mm) drywall, plywood, wood, acoustical tile, ceiling tile, plaster and stucco.

CAT. NO.	UPC NO.	DESCRIPTION
35720	35720	Blade for 35712
35721	35721	Blade for 35713
35722	35722	Blade for 35714
35723	35723	Blade for 35715
35724	35724	Blade for 35716
35725	35725	Blade for 35717
35726	35726	Blade for 35718
35727	35727	Blade for 35719
35708	35708	Set of 5 Blade Screws
35730	35730	Blade for 35728
35731	35731	Blade for 35729

CAT. NO.	UPC NO.	DESCRIPTION	DIAMETER	HOLE WEIGHT		USE FOR
				LBS.	KG	
35712	35712	Steel Toothed	4-3/8" (111 mm)	.76	.34	Mini Juno, Capri,
35716	35716	Carbide Grit	4-3/8" (111 mm)	.74	.34	Marco and Halo
35713	35713	Steel Toothed	6-3/8" (162 mm)	1.2	.54	Halo and Capri
35717	35717	Carbide Grit	6-3/8" (162 mm)	1.1	.50	Halo and Capri
35714	35714	Steel Toothed	6-5/8" (168 mm)	1.3	.59	Juno and Progress
35718	35718	Carbide Grit	6-5/8" (168 mm)	1.3	.59	Juno and Progress
35715	35715	Steel Toothed	6-7/8" (175 mm)	1.3	.59	Lithonia, Marco,
35719	35719	Carbide Grit	6-7/8" (175 mm)	1.4	.64	Lightolier, Progress, Capri and Precolite
35728	35728	Steel Toothed	5-3/8" (137 mm)	.98	.44	Capri, Juno, Lightolier, Progress, and Precolite
35729	35729	Carbide Grit	5-3/8" (137 mm)	.98	.44	Capri, Juno, Lightolier, Progress, and Precolite

Quick Cutter™ Hole Saws



- Quickest, most affordable way to cut perfect holes in ceiling tile.
- Cuts clean, precise holes that ensure no light leakage or poor-fitting installations.
- Self-sharpening, carbide-sprayed cutting tips can cut dozens of holes in very abrasive materials and still stay sharp.
- Stabilizer spring balances cutting forces and offers more control of the tool when drilling drywall.
- Dedicated arbor and pilot drill eliminates changeover time.
- Fits a 3/8" drill chuck and can be used with a cordless drill.
- Included dust shield helps eliminate flying dust and debris.

CAT. NO.	UPC NO.	DESCRIPTION
06923	06923	Quick Cutter Recessed Hole Saw, Adjustable in 1/2" Increments for Cuts of 2-1/2" to 7"