

# POWER MANAGEMENT

Accessories



## AC1031 Enclosure Power Strip Module, Half-Width



AC1031

### ENCLOSURE POWER STRIP MODULE, HALF-WIDTH

Six outlet high-density half-width power strip module designed for On-Q Enclosures.

## 364569-02-V1 Duplex Outlet Power Kit, Surge Protected



364569-02-V1

### DUPLEX OUTLET POWER KIT, SURGE PROTECTED

This power kit includes duplex power outlet, metal "J" box, and faceplate kit.

| PART NO. | PRODUCT      | DESCRIPTION  |
|----------|--------------|--|
| F7526    | AC Power Kit | The AC power kit includes metal "J" electrical box, white duplex receptacle and white faceplate for a complete installation. |

### Power Supplies

|           | PART #          | DESCRIPTION  | VOLTAGE   | AMP    | POWER SUPPLY | USE W/ UPDM* |
|-----------|-----------------|--|-----------|--------|--------------|--------------|
| UNITY     | HA6001          | Integration Module                                 | 24        | 2.5    | PW1060       | No           |
|           | HA6101          | Integration Expansion Module                       | 24        | 2.5    | PW1060       | No           |
|           | HA5202          | TVDI Expander Module                               | 24        | 1.25   | PW1030       | Yes          |
| AUDIO     | AU1001          | lyriQ High Performance Keypad Power Module         | 24        | 2.5    | PW1060       | No           |
|           | AU1002/AU7396   | Standard Performance System                        | 24        | 2.5    | PW1060       | No           |
|           | AU1002/AU7396   | System with 1 or 2 high performance keypads        | 24        | 5      | PW1120       | No           |
|           | AU1002/AU7396   | System with 5 or 6 high performance keypads        | 24        | 10     | PW1240       | No           |
| DATA      | VM7632          | 2X2 Enhanced Bi-Directional Video Amplifier Module | 12-15     | 250 mA | PW7760       | Yes          |
|           | VM7640          | 1X1 Bi-Directional Video Amplifier Module          | 12-15     | 150 mA | PW7760       | Yes          |
|           | DA1101          | 802.11n Wireless Access Point                      | 48VDC PoE | 200 mA | Included     | Yes          |
|           | DA1002          | 5 Port 10/100 Ethernet Switch in single module bay | 12-15     | 300 mA | PW7760       | Yes          |
|           | DA1004          | 4 Port 10/100 Ethernet Switch in single module bay | 12        |        | PW7760       |              |
|           | DA1054          | 4-Port Gigabit Router/Switch                       | 12        |        | PW7760       | Yes          |
| CAMERAS   | DA1008          | 8 Port 10/100 Ethernet Switch in single module bay | 12        |        | PW7760       |              |
|           | DA1458          | 8-Port Gigabit Switch with PoE                     | 48        |        | PW1248       | Yes          |
|           | CM1010          | LCD Display Module                                 | 24        | 2.5    | PW1060       | No           |
|           | CM1011          | Cat 5e Camera Module                               | 12        | 800 mA | PW7725       | Yes          |
|           | CM1048          | Combo Camera & LCD Module                          | 24        | 2.5    | PW1060       | No           |
|           | F1003           | Frequency Agile Mono Modulator, 3 Channel          | 15        | 300 mA | Included     | Yes          |
| INTERCOMS | IC1000 (All)    | Broadcast Intercom Module (standalone)             | 12        | 2.5    | PW7725       | Yes          |
|           | IC1002-XX (All) | Broadcast Intercom Module And Main Console         | 12        | 2.5    | PW7725       | Yes          |
|           | IC5001          | Selective Call Intercom Module                     | 24        | 1.5    | PW1030       | Yes          |

\* UPDM = Universal Power Distribution Module



# UNITY HOME SYSTEM

## System Modules



### HA6001 Integration Module



HA6001

### INTEGRATION MODULE

The Integration Module is the heart of the Unity system, providing the central connection point for Selective Call Intercom, lyriQ Audio, and On-Q Camera systems.

As the intelligence of the system, the Integration Module generates the Graphical User Interface and can be upgraded for additional functionality with software updates.

Notes: Power Supply required. Compatible with PW1060 and PW1100 power supplies. Network required for operation.  
6.25" W x 9" H x .25" D

### AU1002 lyriQ 4 Source, 8-Zone Distribution Module




AU1002

### LYRIQ FOUR SOURCE, 8-ZONE DISTRIBUTION MODULE

Distributes four sources of analog audio and a single source of digital audio to multiple locations in the home.

Notes: Power supply required. (See page 41)  
[See page 106 for more information about lyriQ Audio Systems.]  
5.9" H x 6.5" W

### AU1014 lyriQ Advanced Single Source Distribution Module



AU1014


### LYRIQ ADVANCED SINGLE SOURCE DISTRIBUTION MODULE

Distributes one source of analog audio and a single source of digital audio to multiple locations in the home.

Notes: Power supply required (see page 41).  
[See page 106 for more information about lyriQ Audio Systems.]  
3" H X 6.5" W

# UNITY HOME SYSTEM

## Bill Of Materials



Amp up the Unity Home System with four rooms of high-performance audio, a full Selective Call Intercom system, full RF Lighting Control, four cameras, and two versatile viewing options.


| PRODUCT   | PART #    | QUANTITY | PAGE |
|---|-----------|----------|------|
| Integration Module                                | HA6001    | 1        | 80   |
| LCD Console with High-Performance lyriQ           | HA5010-WH | 1        | 84   |
| Ball Camera                                       | CM5002-WH | 1        | 152  |
| TV Display Interface                              | HA5201-WH | 1        | 154  |
| lyriQ Local Source Input in Studio Design         | AU5008-WH | 3        | 99   |
| lyriQ High-Performance Keypad in Studio Design    | AU5010-WH | 3        | 100  |
| 6.5" 5000 Series In-Ceiling Speaker               | HT5650    | 8        | 117  |
| lyriQ Four-Source, Eight-Zone Distribution Module | AU1002    | 1        | 80   |
| lyriQ High-Performance Power Module               | AU1001    | 1        | 28   |
| lyriQ Flush Mount Single-Source Input             | AU1004-WH | 1        | 99   |
| lyriQ Flush-Mount Triple Source Input             | AU1011-WH | 1        | 99   |
| 4-Port Ethernet Router/Switch                     | DA1004    | 1        | 53   |
| Selective Call Video Door Unit                    | IC5003-AB | 1        | 139  |
| Selective Call Room Unit                          | IC5000-WH | 3        | 139  |
| In-Wall Universal Dimmer                          | DRD4-W    | 4        | 156  |
| In-Wall Whole House Scene Controller              | DRD5-W    | 1        | 157  |
| 1-Gang Studio Wallplate                           | WP5001    | 5        | 26   |
| Plug-in Lamp Module                               | MRP6-W    | 1        | 159  |
| Unity RS232 Lighting Interface                    | LC2354    | 3        | 81   |
| 24 V, 240 W Power Supply Kit                      | PW1240    | 1        | 30   |
| Power Supply for Router                           | PW7760    | 1        | 30   |

# ULTIMATE UNITY HOME SYSTEM

## Bill Of Materials

This Unity Home System provides four rooms of audio, a full Selective Call Intercom System, two cameras, lighting control and two versatile viewing options.

| PRODUCT   | PART #    | QUANTITY | PAGE |
|---|-----------|----------|------|
| Integration Module                                | HA6001    | 1        | 80   |
| LCD Console with lyriQ                            | HA5009-WH | 1        | 84   |
| Ball Camera                                       | CM5002-WH | 1        | 152  |
| TV Display Interface                              | HA5201-WH | 1        | 154  |
| lyriQ Local Source Input in Studio Design         | AU5008-WH | 3        | 99   |
| lyriQ Keypad in Studio Design                     | AU5009-WH | 3        | 100  |
| 6.5" 3000 Series In-Ceiling Speaker               | MS3650    | 4        | 118  |
| lyriQ Four-Source, Eight-Zone Distribution Module | AU1002    | 1        | 80   |
| lyriQ Flush-Mount Single Source Input             | AU1004-WH | 1        | 99   |
| lyriQ Flush-Mount Triple Source Input             | AU1011-WH | 1        | 99   |
| 4-Port Ethernet Router/Switch                     | DA1004    | 1        | 53   |
| Selective Call Video Door Unit                    | IC5003-AB | 1        | 139  |
| Selective Call Room Unit                          | IC5000-WH | 3        | 139  |
| In-Wall Universal Dimmer                          | DRD4-W    | 4        | 156  |
| In-Wall Whole House Scene Controller              | DRD5-W    | 1        | 157  |
| 1-Gang Studio Wallplate                           | WP5001    | 5        | 26   |
| Plug-in Lamp Module                               | MRP6-W    | 1        | 159  |
| Unity RS232 Lighting Interface                    | LC2354    | 1        | 81   |
| 24 V, 120 W Power Supply Kit                      | PW1120    | 1        | 29   |
| Power Supply for Router                           | PW7760    | 1        | 30   |
| Power Supply for Router                           | PW7760    | 1        | 30   |




# PREMIUM UNITY HOME SYSTEM

## Bill Of Materials

This Unity Home System provides three rooms of audio, a full Selective Call Intercom System, two cameras, lighting control and two versatile viewing options.

| PRODUCT  | PART #    | QUANTITY | PAGE |
|--|-----------|----------|------|
| Integration Module                               | HA6001    | 1        | 80   |
| LCD Console with lyriQ                           | HA5009-WH | 1        | 84   |
| lyriQ Local Source Input in Studio Design        | AU5008-WH | 2        | 99   |
| lyriQ Keypad in Studio Design                    | AU5009-WH | 2        | 100  |
| 6.5" 3000 Series In-Ceiling Speaker              | MS3650    | 3        | 118  |
| lyriQ Advanced Single Source Distribution Module | AU1014    | 1        | 80   |
| lyriQ Flush-Mount Single Source Input            | AU1004-WH | 1        | 99   |
| 4-Port Ethernet Router/Switch                    | DA1004    | 1        | 53   |
| Selective Call Video Door Unit                   | IC5003-AB | 1        | 139  |
| Selective Call Room Unit                         | IC5000-WH | 1        | 139  |
| In-Wall Universal Dimmer                         | DRD4-W    | 1        | 156  |
| 1-Gang Studio Wallplate                          | WP5001    | 1        | 35   |
| Unity RS232 Lighting Interface                   | LC2354    | 1        | 96   |
| 24v 120 W Power Supply Kit                       | PW1120    | 1        | 29   |
| Power Supply for Router                          | PW7760    | 1        | 30   |
| 1-Gang Studio Wallplate                          | WP5001    | 5        | 26   |
| Plug-in Lamp Module                              | MRP6-W    | 1        | 159  |
| Unity RS232 Lighting Interface                   | LC2354    | 1        | 81   |
| 24 V, 120 W Power Supply Kit                     | PW1120    | 1        | 38   |
| Power Supply for Router                          | PW7760    | 1        | 30   |
| Power Supply for Router                          | PW7760    | 1        | 30   |



# BASIC UNITY HOME SYSTEM

## Bill Of Materials

Help your homeowners experience truly integrated home systems with the Basic Unity Home System.

| PRODUCT  | PART #    | QUANTITY | PAGE |
|--|-----------|----------|------|
| Integration Module                               | HA6001    | 1        | 80   |
| LCD Console with lyriQ                           | HA5009-WH | 1        | 84   |
| 6.5" 3000 Series In-Ceiling Speakers             | MS3650    | 1        | 118  |
| Selective Call Video Door Unit                   | IC5003-AB | 1        | 139  |
| 4-Port Ethernet Router/Switch                    | DA1004    | 1        | 53   |
| 24 V, 120 W Power Supply Kit                     | PW1120    | 3        | 29   |
| Power Supply for Router                          | PW7760    | 1        | 30   |
| lyriQ Advanced Single Source Distribution Module | AU1014    | 1        | 80   |
| lyriQ Flush-Mount Single Source Input            | AU1004-WH | 1        | 99   |

