


Device Boxes

Armoured and Nonmetallic Sheathed Cable Clamps



CI3102-LSSAX
 "Wraparound" bracket for 1-5/8 in. steel studs. With integral support bracket.




BC1104-LA
 Flush ears.




BC1104-LHA
 Positioning tabs. Provision for external nailing. Two embossed mounting slots for internal screw installation.



CI1104-LMSA
 Mounting strap recessed 1/2 in.



BC1104-LSSAX




CI3004-LSSAX-1
 1 in. recessed brackets for 2-1/2 in. and 3-5/8 in. steel studs. Brackets positioned for 2 layers of 1/2 in. drywall.




Cat. No.	Volume (Cu. in.)	Features		Pryouts ends
		Ears	Bracket	
2 in. Deep — Gangable — 3 in. x 2 in.				
CI3102-LSSAX	12.0	-	"SSX"	4
2-1/2 in. Deep — Gangable — 3 in. x 2 in.				
BC1104-LA	12.5	flush	-	4
BC1104-LHA	12.5	-	P. Tabs	4
CI1104-LMSA	12.5	-	"MS"	4
BC1104-LSSAX	12.5	-	"SSX"	4
3 in. Deep — Gangable — 3 in. x 2 in.				
CI3004-LSSAX-1*	18.0	-	"SSX"	4

* Brackets positioned for 2 layers of 5/8 in. drywall




Steel Stud Boxes

Device Boxes




CI3102-LSSAX




CI3102-SSX




CI1204-3/4-SSX-HV




CI2104-LSSAX




CI2104-LSSA-2X




CI2104-LSSX




CI2104-LSS1X-1




CI2104-LSS2X-1



CI2104-LSS3X-1



CI2104-LSS-2X



CI2104-LSS-3X



CISSX-6



Cat. No.	Volume (Cu. in.)	Width (in.)	Features	Knockouts			Pryouts
			Clamps	1/2 in. ends	1/2 in. bottom	3/4 in. ends	ends
Device Boxes — 2 in. Deep — Gangable — 3 in. High							
CI3102-LSSAX	12.0	2	loomex/BX	-	-	-	4
CI3102-SSX	12.0	2	-	2	-	-	-
Device Boxes — 2-1/2 in. Deep — Pre-Ganged — 3 in. High							
CI1204-3/4-SSX-HV	16.0	2	-	-	-	2	-
CI2104-LSSAX	12.5	2	loomex/BX	-	-	-	4
CI2104-LSSA-2X	25.0	3-3/4	loomex/BX	-	-	-	8
CI2104-LSSA-3X	37.5	5-1/2	loomex/BX	-	-	-	12
CI2104-LSSX	12.5	2	loomex/BX	-	-	-	4
CI2104-LSS1X-1	12.5	2	loomex/BX	-	-	-	4
CI2104-LSS2X-1	25.0	3-3/4	loomex/BX	-	-	-	8
CI2104-LSS3X-1	37.5	5-1/2	loomex/BX	-	-	-	12
CI2104-LSS2X	25.0	3-3/4	loomex/BX	-	-	-	8
CI2104-LSS3X	37.5	5-1/2	loomex/BX	-	-	-	12

Cat. No.	Description
Support Brackets	
CISSX-6	Support bracket extension for 6 in. metal stud