

# Protective Eyewear

## Features:

**Impact resistant polycarbonate lenses** block greater than 99.9% of harmful UVA and UVB radiation up to 400 nanometer.

Permanently bonded **Uvextreme® anti-fog coating** with anti-scratch, anti-static and UV protection properties.


**Adjustable spatulite temples** provide a comfortable customized fit.

**Temple-end holes** for easy lanyard attachment.

Meets the traffic signal color recognition requirements of **ANSI Z80.3-1996**.



### Lens Color



Clear Espresso Dark Gray SCT\* Gray Amber

Uvextreme® and Spectrum Control Technology® (SCT®) are registered trademarks of Sperian Eye & Face Protection, Inc.

\*SCT® = Spectrum Control Technology

## Protective Eyewear – Standard

### Additional Features:

- Meets Mil V<sub>0</sub> ballistic test for impact.
- Soft elastomer brow-guard absorbs, diffuses and deflects impact energy.
- Soft flexible fingers adjust and conform to most nasal profiles reducing slippage.
- Three position ratchet lens inclination adjusts for a custom fit and unsurpassed comfort.
- Lens designed to follow the contour of the cheekbone and create a “zone of protection.”
- Dual 9-base wrap-around lens provides uncompromised peripheral vision.
- Unique ventilation channel delivers an outstanding level of moisture and fog control.



60053

Cat. No.	Frame Color	Lens Color	Environment	Light Intensity	True Color Recognition	Visual Light Transmitted	IR Absorption	Blue Light transmittance	Accidental Arc Protection	Weight (lbs.)
60046	black	dark gray	outdoor	normal to bright	Yes	10%	60%	–	No	.15
60047	black	SCT* gray	outdoor	normal to bright	Yes	15%	>85%	<7%	Yes	.15
60049	black	amber	indoor/ outdoor	normal to low	No	90%	–	–	No	.15
60053	black	clear	indoor	normal to low	Yes	92%	–	–	No	.15
60054	royal blue	clear	indoor	normal to low	Yes	92%	–	–	No	.15
60055	black	espresso	outdoor	normal to bright	Yes	15%	60%	<3%	No	.15

## Protective Eyewear – Frameless

### Additional Features:

- Dual nine-base wrap-around lens with integrated side shields provides a clear, unobstructed field of vision and superior coverage.
- Sleek, frameless design is featherlight (22 grams) for all-day comfort.
- Lens inclination adjustment system for a customized fit.
- Molded-in nose bridge provides uncompromised comfort and fit.



60056

Cat. No.	Frame Color	Lens Color	Environment	Light Intensity	True Color Recognition	Visual Light Transmitted	IR Absorption	Blue Light transmittance	Accidental Arc Protection	Weight (lbs.)
60056	black	clear	indoor	normal to low	Yes	92%	–	–	No	.15
60057	black	espresso	outdoor	normal to bright	Yes	15%	60%	<3%	No	.15

## Protective Eyewear – Full Frame

### Additional Features:

- Superior peripheral protection from side impact.
- Molded-in nose bridge provides uncompromised comfort and fit.
- Contemporary wrap-around lens for exceptional coverage and excellent field of vision.
- Tight wrap-around design provides exceptional brow protection from flying particulates.



60058

Cat. No.	Frame Color	Lens Color	Environment	Light Intensity	True Color Recognition	Visual Light Transmitted	IR Absorption	Blue Light transmittance	Accidental Arc Protection	Weight (lbs.)
60058	black	clear	indoor	normal to low	Yes	92%	–	–	No	.15

**⚠WARNING:** It is important that users of these products read, understand, and follow all instructions, cautions, and warnings that are attached to and/or packed with the product.

