


FIRE CLASSIFIED FLOOR BOXES

880MP Series Floor Boxes

Fire Classified 880MP Series Floor Boxes Nonmetallic Cover Plates Ordering Information


828PR Nonmetallic Duplex Cover Plate



828PR-BLK, 828PR-BRN

Flip lids. Available in black or brown. Can also be used with a 106 type communication adapter.


829PFLRT Nonmetallic Communication Cover Plate



829PFLRT-BLK, 829PFLRT-BRN

Individual flip lids. Available in black or brown. Gasket included. Ortronics® MAB6TJ TracJack and MAB3S2 Series II adapters included.


828PRGFI Nonmetallic GFI Cover Plate



828PRGFI-BLK, 828PRGFI-BRN

Available in black or brown. May be used with Ortronics® Connectivity systems in conjunction with 817, 827 and 837PCC Series flanges.


829PCK Nonmetallic Communication Cover Plate



829PCK-BLK, 829PCK-BRN

Breakouts. Available in black or brown. Feed through only, not for use with a mounting plate for communication jacks.


829PFL Nonmetallic Communication Cover Plate



829PFL-BLK, 829PFL-BRN

Individual flip lids. Available in black or brown. Gasket included. Wiremold CM Series inserts included.

829PSTC Nonmetallic Communications Cover Plate



829PSTC-BLK, 829PSTC-BRN

Data slides. Available in black or brown. Feed through only, not for use with a mounting plate for communication jacks.

MODULINK™ 880MP2 SERIES FLOOR BOXES




Modulink™ Nonmetallic Floor Boxes provide power and communication services directly to the workstation or to any open space location.

CODE REFERENCE

cULus Listed
Nonmetallic Outlet Boxes:
 File E110748 Guide QCMZ.
 Meets Article 314.27(C) of NEC.

Modulink 880MP2 Series Floor Boxes Ordering Information


880MP2 Nonmetallic Rectangular Floor Box



Box comes complete with reusable mudcap, insert spacer, conduit plugs and reducers. Reducers provided for reduction to 1 1/2", 1 1/4", 1", 3/4", and 1/2" [25mm, 19.1mm, and 12.7mm] conduit. Minimum concrete depth is 4" [102mm] and maximum concrete depth is 6" [152mm]. Minimum capacity is 50 cu. in. [819ml] and maximum capacity is 100 cu. in. [1693ml]. Box dimensions are 4 1/8" W x 5 1/2" L x 6" H [105mm W x 140mm L x 152mm H].

NOTE: Insert spacer should not be removed until after concrete pour.
 Box can be connected together to create a two- or three-gang option.

880MPA Nonmetallic Rectangular Floor Box Adjusting Ring



Comes with fiber storage loop. Also includes brass inserts for flange connection and green ground wire for ground connection. Wiremold CM Series Open System adapters that snap directly into the adjusting ring without the need for an adapter. Also includes mounting screws to attach flange to box body.

NOTE: One 880MPA is needed for each 880MP2 used. For example, a three-gang box will require three 880MPA Adjusting Rings, ordered separately.

COLOR OPTIONS




817, 828, 829, 830, 837 & 838 Series Cover Plates are designed for use with Modulink™ 880MP Series Floor Boxes and are available in the colors at left as indicated in the part number descriptions.

Custom color options are also available. Consult the factory for more information.


OMNIBOX™ SERIES FLOOR BOXES

Omnibox Series Nonmetallic Cover Plate Flanges Ordering Information (continued)


837PCC 3-Gang Nonmetallic Carpet Flange**837PCC-BLK, 837PCC-BRN**

For Ortronics® connectivity use with 829PFLRT Cover. For Activate™ connectivity use with 829PFL Cover. Accepts Ortronics® MAB6TJ TracJack and MAB3S2 Series II adapters and Wiremold CM Series inserts, sold separately.


Omnibox Series Nonmetallic Cover Plates Ordering Information

828PR Nonmetallic Duplex Cover Plate**828PR-BLK, 828PR-BRN**


Flip lids. Can also be used with a 106 type communication adapter.

829PFLRT**Nonmetallic Communication Cover Plate****9829PFLRT-BLK, 829PFLRT-BRN**


Individual flip lids. Gasket included. Ortronics® MAB6TJ TracJack and MAB3S2 Series II adapters included.

828PRGFI Nonmetallic GFI Cover Plate**828PRGFI-BLK, 828PRGFI-BRN**


May be used with Ortronics® Connectivity systems in conjunction with 817, 827 and 837PCC Series flanges.

829PCK**Nonmetallic Communications Cover Plate****829PCK-BLK, 829PCK-BRN**

Breakouts. Feed through only, not for use with a mounting plate for communication jacks.

829PFL Nonmetallic Communication Cover Plate**829PFL-BLK, 829PFL-BRN**

Individual flip lids. Gasket included. Wiremold CM Series inserts included.

829PSTC**Nonmetallic Communications Cover Plate****829PSTC-BLK, 829PSTC-BRN**

Data slides. Feed through only, not for use with a mounting plate for communication jacks.

NOTE: UL Listed for tile, terrazzo, and carpet floors. Brass covers and flanges are not interchangeable with aluminum or nonmetallic covers and flanges. Nonmetallic covers are interchangeable with aluminum flanges.