




System Features and Benefits

- Up to four sources per multi-source system
- Up to eight zones per multi-source system, with ability to expand
- Whole house control via universal remote and keypad
- High performance and standard systems
- Up to two local source inputs per keypad
- Flush mount inputs in single and triple source versions
- Classic design enhances any decor
- Efficient installation via Cat 5 wiring

COLORS



RELATED PRODUCTS



F7417-XX
lyriQ Local Source
Input



AU7394-XX
lyriQ Keypad




AU1000-XX
lyriQ High-Performance
Keypad



AU7400-XX
lyriQ Single Source, 4-Zone Kit

WIRING DIAGRAM



INSTALLATION AT-A-GLANCE lyriQ SINGLE-SOURCE AUDIO SYSTEM

1. Run a Cat 5 cable from the On-Q enclosure to a single gang box at each location where a keypad or lyriQ Local Source Input will be installed. Also run a Cat 5 cable at any Local Source Input location to a single gang box where its associated keypad will be installed.
2. Install each lyriQ Keypad in a single gang box after connecting a pair of speakers to each keypad with 16/2 speaker wire. Also install the lyriQ Local Source Input in its single gang box.
3. Install the lyriQ Single Source Four-Zone Distribution Module in the On-Q enclosure and connect the Cat 5 cables from the keypads and lyriQ Local Source Input.
4. Run a Cat 5 cable from the lyriQ Single Source Four-Zone Distribution Module to a single gang box containing the lyriQ Flush-Mount Single Source Input and connect the audio source to the lyriQ Flush-Mount Single Source Input with RCA cables.



lyriQ SOURCE INPUTS

PRODUCT	PART #	DESCRIPTION	DIMENSIONS
lyriQ Local Source Input 	F7417-BK F7417-IV F7417-LA F7417-WH	The lyriQ Local Source Input enables users to plug in devices locally for in-room entertainment. Listen to personal audio players, enjoy video games and watch TV with rich sound output to local speakers. The local source input automatically overrides the remote source music in the room and returns to the main source when the local source is turned off. Wall plate not included.	4.2" H x 1.65" W
lyriQ Flush Mount Triple Source Input 	AU1011-BK AU1011-LA AU1011-WH	The lyriQ Flush Mount Triple Source Input connects to the Four-Source, Eight-Zone Module to distribute three audio sources throughout the home. It features two RJ45 connections, adjustable gain control for each input, three IR emitter ports and one IR target port. Pair with the lyriQ Single Source Input in flush-mount or standard versions (AU1004 or F7398). Wall plate not included.	4.2" H x 3.3" W
lyriQ Flush Mount Single Source Input 	AU1004-BK AU1004-LA AU1004-WH	The lyriQ Flush Mount Single Source Input connects to a lyriQ distribution module to distribute one audio source throughout the home. It features an RJ45 connection, adjustable gain control, an IR emitter port and an IR target port. Wall plate not included.	4.2" H x 1.65" W
lyriQ Triple Source Input 	F7428	The lyriQ Triple Source Input connects to the Four-Source, Eight-Zone Module to distribute three audio sources throughout the home. It features two RJ45 connections, adjustable gain control for each input, three IR emitter ports and one IR target port. Pair with the lyriQ Single Source Input in flush-mount or standard versions (AU1004 or F7398).	2.45" H x 4.5" W x 1.25" D
lyriQ Single Source Input 	F7398	The lyriQ Single Source Input connects to a lyriQ distribution module to distribute one audio source throughout the home. It features an RJ45 connection, adjustable gain control, an IR emitter port and an IR target port.	2.45" H x 4.5" W x 1.25" D

COLOR OPTIONS





lyriQ KIT CONTENTS

PART NO.	STYLE		DISTRIBUTION MODULES				SOURCE INPUTS					KEYPADS			POWER			ACCESSORIES										
	STUDIO	CLASSIC	COLORS	AU1002	AU7396	AU1014	AU1001	AU7398	AU1004-XX	F7428	AU1011-XX	AU5008-XX	F7417-XX	AU5009-XX	AU5010-XX	AU7394-XX	AU1000-XX	F7399-XX	PW1060	PW1120	PW1240	AU1060	F7425	WP50001-XX	WP1205-XX	WP50002-XX	WP1207-XX	
lyriQ High Performance																												
AU5646-WH	●	WH		●				●	●	●				6						●		●	●	7		1		
AU5644-WH	●	WH		●				●	●	●				4				●	●			●	●	5		1		
lyriQ Standard																												
AU5544-XX	●	WH LA		●				●	●	●				4														
AU5514-WH	●	WH																										
AU5412-WH	●	WH																										
High Performance Six Zone																												
AU1006-XX		● WH LA																										
High Performance Four Zone																												
AU1005-XX		● WH LA																										
Four Zone w/ Flush Mount Input																												
AU1021-XX		● WH LA																										
AU1012-XX		● WH LA																										
Four Zone w/ Surface Mount Input																												
AU1003-XX		● WH LA																										
AU1007-XX		● WH LA																										
AU7400-XX		● WH LA																										
AU7395-WH		● WH																										
Two Zone w/ Flush Mount Input																												
AU9020-WH		● WH																										