

Square Boxes and Accessories




CAT. NO.	(IN.)	CAPACITY	CTN.
For Single Device			
72 C 62	1/4	1.0	25
72 C 13	1/2	3.0	25
72 C 14	3/4	5.0	25
72 C 14 5/8	5/8	4.0	25
72 C 15	1	7.0	10
72 C 16	1¼	8.3	10
For Two Devices			
72 C 17	1/2	6.3	25
72 C 18	3/4	9.0	25
72 C 18 5/8	5/8	7.5	25
72 C 19	1	12.0	25
72 C 21	1¼	15.0	25

4¹¹/₁₆¹¹ Square-Cut Tile Wall Covers



CAT. NO.	RAISED (IN.)	CU. IN. Capacity	STD. CTN.
For Single Device — Steel			
72-C-49-1/2	1/2	3.5	10
72 C 49 3/4	3/4	5.3	10
72-C-49-1	1	7.0	10
72-C-49-1-1/4	11⁄4	7.0	10
72 C 50 1 1/2	11/2	9.0	10
72 C 51 2	2	14.5	20
For Two Devices — Steel			
72-C-52-1/2	1/2	6.0	10
72 C 52 3/4	3/4	9.0	10
72-C-52-1	1	12.5	25
72-C-52-1-1/4	11⁄4	15.5	25
72 C 53 1 1/2	11/2	19.0	10
72 C 54 2	2	25.5	10

4¹/₁₆" Square Industrial Device Covers



CAT. NO.	CU. IN. Capacity	DESCRIPTION	STD. CTN.
649	7.5	¹ / ₂ " raised — 4 ¹ / _λ ₆ " square Surface blank. Each cover individually packaged with the necessary screws for mounting*	10
650-BW	7.5	1/4" raised — 411/6" square For one toggle switch and one single receptacle. Opening 1.4" diameter. Each cover individually packaged with the necessary screws for mounting*	10
655	7.5	½" raised — 4 ¹ / _λ e" square For two single receptacles. Opening 1.4" diameter. Each cover individually packaged with the necessary screws for mounting*	10
657-NEC	7.5	½" raised — 4 ¹ / ₆ " square For one duplex and one single receptacle. Opening 1.4" diameter. Each cover individually packaged with the necessary screws for mounting*	10
663-BW	7.5	½" raised — 41%,6" square For two three-wire twist lock receptacles. 11/16" spacing between 1.4" diameter openings. Each cover individually packaged with the necessary screws for mounting*	10
665-BW	7.5	¹ ⁄⁄₂" raised — 4 ¹ ⁄ ₁ / ₅ " square Opening to accommodate Hubbell 3330 receptacle in center. Opening 1.75" diameter. Each cover individually packaged with the necessary screws for mounting*	10

*Fits any Steel City® 411/16" square outlet box or extension ring.

.



United States Tel: 901.252.8000 800.816.7809 Fax: 901.252.1354 Technical Services Tel: 888.862.3289

