

# MODULINK™ 880MP2 SERIES FLOOR BOXES




Modulink™ Nonmetallic Floor Boxes provide power and communication services directly to the workstation or to any open space location.

## CODE REFERENCE

**cULus Listed**  
**Nonmetallic Outlet Boxes:**  
 File E110748 Guide QCMZ.  
 Meets Article 314.27(C) of NEC.

## Modulink 880MP2 Series Floor Boxes Ordering Information


### 880MP2 Nonmetallic Rectangular Floor Box



Box comes complete with reusable mudcap, insert spacer, conduit plugs and reducers. Reducers provided for reduction to 1 1/2", 1 1/4", 1", 3/4", and 1/2" [25mm, 19.1mm, and 12.7mm] conduit. Minimum concrete depth is 4" [102mm] and maximum concrete depth is 6" [152mm]. Minimum capacity is 50 cu. in. [819ml] and maximum capacity is 100 cu. in. [1693ml]. Box dimensions are 4 1/8" W x 5 1/2" L x 6" H [105mm W x 140mm L x 152mm H].

**NOTE:** Insert spacer should not be removed until after concrete pour.  
 Box can be connected together to create a two- or three-gang option.

### 880MPA Nonmetallic Rectangular Floor Box Adjusting Ring



Comes with fiber storage loop. Also includes brass inserts for flange connection and green ground wire for ground connection. Wiremold CM Series Open System adapters that snap directly into the adjusting ring without the need for an adapter. Also includes mounting screws to attach flange to box body.

**NOTE:** One 880MPA is needed for each 880MP2 used. For example, a three-gang box will require three 880MPA Adjusting Rings, ordered separately.

## COLOR OPTIONS




817, 828, 829, 830, 837 & 838 Series Cover Plates are designed for use with Modulink™ 880MP Series Floor Boxes and are available in the colors at left as indicated in the part number descriptions.

**Custom color options are also available. Consult the factory for more information.**

# MODULINK™ 880MP2 SERIES FLOOR BOXES

## Modulink 880MP2 Series Floor Boxes Nonmetallic Cover Plates Flanges Ordering Information


### 817PCC 1-Gang Nonmetallic Carpet Flange



#### 817PCC-BLK, 817PCC-BRN

Available in black or brown. For Ortronics® connectivity use with 829PFLRT Cover. For Activate connectivity use with 829PFL Cover. Accepts Ortronics® MAB6TJ TracJack and MAB3S2 Series II adapters and Wiremold CM Series inserts, sold separately.


### 837PCC 3-Gang Nonmetallic Carpet Flange



#### 837PCC-BLK, 837PCC-BRN

Available in black or brown. For Ortronics® connectivity use with 829PFLRT Cover. For Activate connectivity use with 829PFL Cover. Accepts Ortronics® MAB6TJ TracJack and MAB3S2 Series II adapters and Wiremold CM Series inserts, sold separately.

### 827PCC 2-Gang Nonmetallic Carpet Flange




#### 827PCC-BLK, 827PCC-BRN

Available in black or brown. For Ortronics® connectivity use with 829PFLRT Cover. For Activate connectivity use with 829PFL Cover. Accepts Ortronics® MAB6TJ TracJack and MAB3S2 Series II adapters and Wiremold CM Series inserts, sold separately.

**NOTE: Brass covers and flanges are not interchangeable with aluminum or nonmetallic covers and flanges. Nonmetallic covers are interchangeable with aluminum flanges.**

## Modulink 880MP Series Floor Boxes Nonmetallic Cover Plates Ordering Information


### 828PR Nonmetallic Duplex Cover Plate



#### 828PR-BLK, 828PR-BRN

Flip lids. Available in black or brown. Can also be used with a 106 type communication adapter.


### 829PFLRT\* Nonmetallic Communication Cover Plate



#### 829PFLRT-BLK, 829PFLRT-BRN

Individual flip lids. Available in black or brown. Gasket included. Ortronics® MAB6TJ TracJack and MAB3S2 Series II adapters included.


### 828PRGFI Nonmetallic GFI Cover Plate



#### 828PRGFI-BLK, 828PRGFI-BRN

Available in black or brown. May be used with Ortronics® Connectivity systems in conjunction with 817, 827 and 837PCC Series flanges.


### 829PCK Nonmetallic Communication Cover Plate



#### 829PCK-BLK, 829PCK-BRN

Breakouts. Available in black or brown. Feed through only, not for use with a mounting plate for communication jacks.


### 829PFL\* Nonmetallic Communication Cover Plate



#### 829PFL-BLK, 829PFL-BRN

Individual flip lids. Available in black or brown. Gasket included. Wiremold CM Series inserts included.

### 829PSTC Nonmetallic Communications Cover Plate



#### 829PSTC-BLK, 829PSTC-BRN

Data slides. Available in black or brown. Feed through only, not for use with a mounting plate for communication jacks.

\*Replacement flip lids can be ordered under Cat. No. PFL-BLK and PFL-BRN. Each Cat. No. comes with three flip lids. The above cover plates are listed for tile and carpet applications.