

6x4 FiberRunner® QuikLock™ Coupler

- Pre-assembled to provide fast mechanical assembly of components
- No tools required for installation; bolts loosen for component disassembly



Part Number	Part Description	Std. Pkg. Qty.	Std. Ctn. Qty.
FRBC6X4YL	Pre-assembled coupler quickly joins two sections of channel and/or fittings. Mechanically attaches without tightening bolts. Bolts release using 3/8" nut driver to allow coupler to be removed if necessary.	1	5

For a bulk package of 20 couplers, order FRBC6X4YL-E.
For other colors replace YL (Yellow) with OR (Orange) or BL (Black).

6x4 FiberRunner® System Fittings

- Minimum 2" (50.8mm) bend radius control fittings
- Optional split covers snap onto each fitting
- Protect against signal loss and performance degradation
- Covers feature 3/4" (19mm) gap to allow cable to be laid in
- Assemble using FRBC QuikLock™ Couplers

Part Number	Part Description	Couplers Required	Std. Pkg. Qty.	Std. Ctn. Qty.
-------------	------------------	-------------------	----------------	----------------

6x4 Horizontal Right Angle Fitting

FRRA6X4YL	Attaches to 6x4 channel and/or fittings to create a 90° horizontal turn from a straight horizontal run. Accepts optional split cover FRRASC6YL.	(2 pcs.) FRBC6X4YL	1	5
-----------	---	-----------------------	---	---



FRRA6X4

Split Cover for 6x4 Horizontal Right Angle Fitting

FRRASC6YL	Optional split cover for the horizontal right angle fitting FRRA6X4YL. Snap-on feature allows cover to be installed and removed with no tools required. Creates radiused 3/4" (19mm) opening for easy access to add or remove cables.	—	1	5
-----------	---	---	---	---



FRRASC6

6x4 Horizontal 45° Angle Fitting

FRH456X4YL	Attaches to 6x4 channel and/or fittings to create a 45° horizontal turn from a straight horizontal run. Accepts optional split cover FRH45SC6YL.	(2 pcs.) FRBC6X4YL	1	5
------------	--	-----------------------	---	---



FRH456X4

Split Cover for 6x4 Horizontal 45° Angle Fitting

FRH45SC6YL	Optional split cover for the horizontal 45° angle fitting FRH456X4YL. Snap-on feature allows cover to be installed and removed with no tools required. Creates radiused 3/4" (19mm) opening for easy access to add or remove cables.	—	1	5
------------	--	---	---	---



FRH45SC6

6x4 Horizontal 45° Angle Fitting

FRT6X4YL	Attaches to 6x4 channel and/or fittings to create a 90° horizontal branch from a straight horizontal run. Accepts optional split cover FRTSC6YL.	(3 pcs.) FRBC6X4YL	1	5
----------	--	-----------------------	---	---



FRT6X4

Split Cover for 6x4 Horizontal Tee Fitting

FRTSC6YL	Optional split cover for the horizontal tee fitting FRT6X4YL. Snap-on feature allows cover to be installed and removed with no tools required. Creates radiused 3/4" (19mm) opening for easy access to add or remove cables.	—	1	5
----------	--	---	---	---



FRTSC6

For other colors replace YL (Yellow) with OR (Orange) or BL (Black).

Continues on next page