

		Page	Base Material											Anchor Diameter											Head Style				Coating/ Material											
			Concrete	Lightweight Concrete	Hollow Core Plank	Grout-filled Concrete Masonry	Hollow Concrete Masonry	Solid Brick	Hollow Brick	Stone	Structural Clay/Tile	Plywood	Wallboard / Plaster	No. 4 Screw	No. 5 Screw	No. 6 Screw	No. 7 Screw	No. 8 Screw	No. 9 Screw	No. 10 Screw	No. 12 Screw	No. 14 Screw	No. 16 Screw	No. 18 Screw	1/8"	3/16"	1/4"	5/16"	3/8"	1/2"	Finished (Hex) Head	Round Head	Flat Head (Countersunk)	Mushroom Head	Removable	Coated / Plated Carbon Steel	Zamac Alloy	Nylon Plastic	Lead	
Metal Anchors	Wall Dog	42	●	○	○	●	●	●	○		●	●															●		●											
	Scru-Lead	42	●	○	○	○	●	●	●	○					●	●	●		●	●	●	●	●															●		
	Toggle-Bolt	42			○		●		○		○	●	●												●	●	●	●	●	●	●	●	●	●	●	●	●	●		
	Polly	43			○		●			○	●	●													●	●	●			●	●					●	●			
	Legs	43										●		●	●	●																				●				
	Zip-All	44										●	●		●	●	●																	●		●				
Plastic Anchors	Sharkie	44	●	●	●	●	○	●	○	●	○	●	●	●	●	●	●	●	●	●	●	●																●		
	Strap-Toggle	44			○		●		○		○	○	●					●	●	●						●	●		●	●	●					●		●		
	Zip-It / Zinc Zip-It	44										●		●	●	●																		●		●	●			
	Zip-Toggle	45										○	●		●																						●			
	Poly-Toggle	45	●	○	○	○	○	○	○	○	○	●	●		●	●	●	●	●	●	●																	●		
	Pop-Toggle	45	○	○	○	○	●	○	○	○	○	●	●		●	●	●	●	●	●	●	●															●			
	Bantam Plug	45	●	○	○	○	●	●	●				●		●	●	●	●	●	●	●	●	●														●			
	Fluted Plastic	45	●	○	○	○	○	○	○			○	●	●	●	●	●	●	●	●	●	●	●														●			

● Suitable

○ May be Suitable

## Wall Dog®

### Universal Light-Duty Anchor

#### BASE MATERIAL

Wallboard (1/2", 5/8" & double wallboard), Plywood, Concrete, Hollow or Grout Filled Block, Brick, Plaster, Wood and Masonry

#### SIZE RANGE

3/16" Diameter x 2-1/2" Length max.

#### ANCHOR MATERIAL

Case Hardened Carbon Steel



Powers' Wall Dog is the industry's first all steel one-piece screw anchor, featuring high-profile threads for easy fastening into wallboard & other masonry base materials. Its deep cutting, corkscrew-like threads provide for smooth entry and a strong hold. When removed, the Wall Dog leaves a much smaller hole than toggles or other systems. For fastening into wallboard or wood, no pre-drilling is required. Fastening into concrete, hollow or grout filled block, brick and plaster requires a pre-drilled 3/16" ANSI hole.

#### Features and Benefits

- Installs in wallboard, plywood, concrete, hollow or grout filled block, brick and plaster
- Patented design provides for smooth entry, clean cutting and a strong hold
- Thread design prevents spinning and stripping
- Heat treated point can penetrate metal and wood studs
- Various head styles and colors available
- Self-drills in wallboard and in plywood
- Installs quickly and easily with a Phillips® screwdriver



#### WALL-DOG LIGHT DUTY ANCHOR - COMBO HWH

CAT. NO.	DESCRIPTION	STD. BOX	STD. CTN.	MASTER CTN.
2265	1-1/4" Combo HWH Zinc			5000
2271	1-1/4" Combo HWH Zinc	100	1000	N/A



#### WALL-DOG LIGHT DUTY ANCHOR - WAFER HEAD

CAT. NO.	DESCRIPTION	STD. BOX	STD. CTN.	MASTER CTN.
2277	1/4" x 1-1/2" White Wafer Head	100	500	N/A
2278	1/4" x 2" White Wafer Head	100	500	N/A
2279	1/4" x 2-1/4" White Wafer Head	100	500	N/A
2280	1/4" x 2-1/2" White Wafer Head	100	500	N/A

Phillips® is a registered trademark of Phillips Consumer Electronics Corporation.



#### WALL-DOG LIGHT DUTY ANCHOR - ROBERTSON HEAD

CAT. NO.	DESCRIPTION	STD. BOX	STD. CTN.	MASTER CTN.
2281	1-1/4" Zinc Robertson Head			5000
2266	1-1/4" Zinc Robertson Head	100	1000	N/A



#### WALL-DOG LIGHT DUTY ANCHOR - OVAL HEAD

CAT. NO.	DESCRIPTION	STD. BOX	STD. CTN.	MASTER CTN.
2314	1-1/4" Zinc Oval Head	100	1000	N/A
2328	1-1/4" White Oval Head	100	1000	N/A
2288	1-1/4" Black Oval Head	100	500	N/A
2292	1-1/4" Brass Oval Head	100	500	N/A



#### WALL-DOG LIGHT DUTY ANCHOR - PAN HEAD

CAT. NO.	DESCRIPTION	STD. BOX	STD. CTN.	MASTER CTN.
2316	1-1/4" Zinc Pan Head	100	1000	N/A
2330	1-1/4" White Pan Head	100	1000	N/A
2273	1-1/2" White Pan Head	100	600	N/A

CAT. NO.	DESCRIPTION	STD. BOX	STD. CTN.	MASTER CTN.
2274	1-1/2" Bronze Pan Head	100	600	N/A
2275	1-1/2" Zinc Pan Head	100	600	N/A
2276	1-1/2" Black Phosphate Pan Head	100	600	N/A
2286	1-1/4" Black Pan Head	100	500	N/A
2294	1-1/4" Brass Pan Head	100	500	N/A



#### WALL-DOG KIT (SCREWDRIVER)

PACKAGED WITH 50 ZINC PANHEAD ANCHORS AND 1 PHILLIPS® SCREWDRIVER

CAT. NO.	DESCRIPTION	STD. BOX	STD. CTN.
2289	Wall-Dog Kit with Screwdriver	1	10

#### WALL-DOG KIT (BIT)

PACKAGED WITH 50 ZINC PANHEAD ANCHORS AND 3/16" STRAIGHT SHANK BIT

CAT. NO.	DESCRIPTION	STD. BOX	STD. CTN.
2332	Wall-Dog Kit with Drill Bit	1	10



## Scru-Lead

### Wall Anchor

#### BASE MATERIAL

Concrete, Block, Brick

#### SIZE RANGE

No. 6-8 x 3/4" to No. 16-18 x 1-1/2"

#### ANCHOR MATERIAL

Lead Alloy

The Scru-Lead anchor is designed for use with sheet metal or wood screws in concrete, block or brick. Made entirely of lead alloy which is soft enough for easy installation, yet hard enough to give holding strength, the performance of this product is dependent on the integrity of the base material.

CAT. NO.	SIZE	DRILL DIA.	MIN. DEPTH	STD. BOX	STD. CTN.
9409	6-8 x 3/4"	1/4"	3/4"	100	1000
9414	6-8 x 1"	1/4"	1"	100	1000
9419	6-8 x 1-1/2"	1/4"	1-1/2"	100	500
9429	10-14 x 1"	5/16"	1"	100	500
9439	10-14 x 1-1/2"	5/16"	1-1/2"	100	500
9460	16-18 x 1-1/2"	3/8"	1-1/2"	25	250

## Toggle Bolt

### Hollow Wall Anchor

#### BASE MATERIAL

Hollow Block, Wallboard, Plaster


#### SIZE RANGE

1/8" x 2" to 1/2" x 4"

#### ANCHOR MATERIAL

Carbon Steel

The Toggle Bolt is a spring wing type hollow wall anchor designed for use in block, wallboard and other hollow base materials. A two-part assembly consisting of a machine screw and a spring wing toggle, sizes range from 1/8" x 2" to 1/2" x 4" with combo round, flat, mushroom, tie-wire or slotted hex head styles.



#### COMBO MUSHROOM HEAD

CAT. NO.	SIZE	DRILL DIA.	STD. BOX	STD. CTN.
4023	1/8" x 2"	3/8"	50	500
4033	1/8" x 3"	3/8"	50	500