400, 800, 2300 & 2300D SERIES™ RACEWAYS

Two-Piece, Single- and Dual-Channel, Low Profile



Two-piece, single- and dual-channel, low profile raceway. Easy-toinstall and ideal for power or communication installations.


CODE REFERENCE

cULus Listed Raceway: File E90378 Guide RJTX. Complies with flammability requirements of UL-5A.

Fittings:

File E90377 Guide RJYT. Meets Article 388 of NEC. UL Listed for up to 600V. Meets Section 12-1600 of CEC.

400, 800, 2300 & 2300D Series Raceways System Layout



NOTE: Illustration is for showing product applications only.

KEY

- A. 406, 806, 2306 Cover Clip
- B. 411, 811, 2311, 2311DFO Flat Elbow Fitting
- **C.** 810A2, 2310A, 2310DFO Entrance End Fitting **D.** 415, 815, 2315 Tee

- E. 417, 817, 2317, 2317DFO Internal Elbow
- **F.** 418, 818, 2318, 2318DFO External Elbow
- G. 2337A, 2338A Round Device Boxes
- H. 2344, 2347, 2348 Sure-Snap Device Boxes

COLOR OPTIONS



400, 800, 2300 Series Raceway Part Numbers with a "-WH" suffix have a white finish. Part Numbers without a suffix have an ivory finish. 400, 800, 2300 Series Raceways are paintable using latex paint.


Custom color options are also available. Consult the factory for

400, 800, 2300 & 2300D SERIES™ RACEWAYS

Ordering Information


2300/2300D Series Raceway Ordering Information

2300BAC Raceway Base and Cover



Low-profile, two-piece raceway with durable, textured PVC ivory or white finishes. Available in 5' [1.52m] lengths. Packed 50' [15.2m] per carton. Supplied with wide adhesive tape along its entire length. Also available in white (2300BAC-WH).

2300BACD Divided Raceway Base and Cover



Low-profile, two-piece raceway with durable, textured PVC ivory or white finishes. Available in 5' [1.52m] lengths. Supplied with wide adhesive tape along its entire length. Also available in white (2300BACD-WH).

PVC-1 PVC Raceway Cutter



Regular duty cutter. Ideal for use with small nonmetallic raceways.

2300WC Wire Clip



For holding conductors in place.

2306 Cover Clip




For covering joint where two pieces of 2300BAC and 2300BACD Series Raceway Cover come together. Also available in white (2306-WH).

2310A Entrance End Fitting




For connecting 2300 Series Raceway with 1/2", 3/4", or 1" trade size conduit or armored cable. 1/2" and 3/4" trade size KO on end, 1/2", 3/4", and 1" trade size KOs on bottom. Also available in white [23120A-WH].

2310B Blank End Fitting




For closing open end of 2300BAC and 2300BACD Series Raceways. Also available in white (2310B-WH).

2311 Flat Elbow




For right angle turns on same surface. Also available in white (2311-WH).

2315 Tee



For branching of raceway running at right angles. Also available in white (2315-WH).

2317 Internal Elbow




For right angle turns around internal corners. Also available in white (2317-WH).

2318 External Elbow



For right angle turns around external corners. Also available in white (2318-WH).

2389 Reducing Connector



For transitioning from 2300 Series Raceway to 800 Series Raceway. Also available in white (2389-WH).

NOTE: Device Boxes for 2300 and 2300D Series Raceway can be found on the next page of this product section.