




Straight blade devices

Complex environment straight blade devices

Product description

2-pole, 3-wire grounding
20A, 125V/AC
NEMA 5-20



Plugs & connectors



Rating A	V/AC	NEMA	Description	Cord diameter	Color	Plug catalog no.	Connector catalog no.		
20	125	5-20	Watertight	0.30-0.65" (7.6-16.5mm)	Y	□ 14W33*	□ 15W33*	•	•
			Watertight	0.30-0.65" (7.6-16.5mm)	BK	□ 14W33BK*	□ 15W33BK*	•	•
			Severe duty	0.38-1.00" (9.7-25.4mm)	Y & BK	□ 1433*	□ 1533*	•	•
			Auto grip corrosion resistant	0.33-0.66" (8.4-16.7mm)	Y	□ 5366NCR	□ 5369NCR	•	•

* Not Fed Spec

Receptacles, back & side wire



Rating A	V/AC	NEMA	Description	Color	Single receptacle catalog no.	Duplex receptacle catalog no.		
20	125	5-20	Watertight	Y	□ 60W33	□ 60W33DPLX	•	•
			Watertight	BK	□ 60W33BK	□ 60W33DPLXBK	•	•
			Corrosion resistant	Y	--	□ AH5362CRY	•	•
			Corrosion resistant	GY	--	□ AH5362CRGY	•	•

Accessories for watertight 15/20A plugs & connectors

Description	Cord diameter	Catalog no.		
Watertight plug closure cap for 15A plug, yellow		□ 14W	•	•
Watertight plug closure cap for 15A plug, black		□ 14WBK	•	•
Replacement watertight connector closure cap for 15A connector, yellow		□ 15W	•	•
Replacement watertight connector closure cap for 15A connector, black		□ 15WBK	•	•
Wire mesh grip for 15/20A watertight plugs & connectors	0.31-0.37" (7.9-9.4mm)	□ WTM131	•	•
Wire mesh grip for 15/20A watertight plugs & connectors	0.38-0.44" (9.7-11.1mm)	□ WTM138	•	•
Wire mesh grip for 15/20A watertight plugs & connectors	0.43-0.50" (10.9-12.7mm)	□ WTM143	•	•
Wire mesh grip for 15/20A watertight plugs & connectors	0.50-0.56" (12.7-14.3mm)	□ WTM150	•	•
Wire mesh grip for 15/20A watertight plugs & connectors	0.56-0.63" (14.3-15.9mm)	□ WTM156	•	•



Dimensional information: D-9

Specification information:

Watertight industrial plugs & connectors: D-36
Severe duty industrial plugs & connectors: D-37
Corrosion resistant auto grip industrial plugs & connectors: D-37

Color information:

BK (Black), Y (Yellow)



Compliances, specifications and availability are subject to change without notice.

Indicates NAFTA compliant - Page Q-32

RoHS compliant - Page Q-32