

Resi-Gard™ Resi-Gard™ Flexible Raceway

(Approved for low voltage use only)

Ideal for providing a main chase from the main distribution panel to a secondary hub in the attic or basement. Resi-Gard™ nonmetallic flexible raceway is available in 3/4 in. to 2 in. diameter sizes with factory installed pull tape in sizes 1 in. to 2 in. The raceway is hand bendable, lightweight and easily cut to length to reduce scrap. Bright orange colour clearly signifies a low voltage installation.

Standard Length Coils

Cat. No.	Size (in.)	Pull Tape	Coil Length	Prod. Wt. (lb.) Coil
SCE4X1-100	3/4	Empty	100	11.5
SCF4X1C-100	1	900 lb.		17.9
SCG4X1C-100	1-1/4			21.5
SCH4X1C-50	1-1/2		50	11.2
SCJ4X1C-50	2	13.4		

Standard Length Reels

Cat. No.	Size (in.)	Pull Tape	Reel Length	Prod. Wt. (lb.) Reel
SCE4X1-1000	3/4	Empty	1000	115.0
SCF4X1C-1500	1	900 lb.	1500	268.5
SCJ4X1C-500	2		500	133.5



Resi-Gard™ Fittings

A complete line of Carlton® one-piece quick connect couplings, threaded adapters and snap-in terminator adapters are available for quick, easy professional installation of Resi-Gard™ flexible raceway.

Quick Connect Snap-In Adapters



Cat. No.	Size (in.)	Std. Ctn. Qty.	Std. Ctn. Wt. (lb.)
SCA253E	3/4	25	0.783
SCA253F	1	20	0.918

Quick Connect Couplings



Cat. No.	Size (in.)	Std. Ctn. Qty.	Std. Ctn. Wt. (lb.)
SCA240E	3/4	25	0.783
SCA240F	1	20	0.972

Male Terminal Adapters*



Cat. No.	Size (in.)	Std. Ctn. Qty.	Std. Ctn. Wt. (lb.)
SCE943G	1-1/4	50	3.0
SCE943H	1-1/2	25	2.5
SCE943J	2	50	6.8

Quick Connect Threaded Adapters



Cat. No.	Size (in.)	Std. Ctn. Qty.	Std. Ctn. Wt. (lb.)
SCA243E	3/4	25	0.633
SCA243F	1	20	0.778

Standard Couplings*



Cat. No.	Size (in.)	Std. Ctn. Qty.	Std. Ctn. Wt. (lb.)
SCE940G	1-1/4	30	3.5
SCE940H	1-1/2	25	3.9
SCE940J	2	30	5.2

*Must be cemented to Resi-Gard™ Flexible Raceway using ONLY Resi-Gard™ Solvent Cement.