



2-160-T Demi MR16



The traditional spherical shape breaks the ceiling with style and elegance. Durable die cast components guarantee rock-solid Tilt and a refined appearance over time.

FEATURES

- Utilizes MR16
- 30° Tilt
- Powder coated and plated trim ring finishes
- Accepts up to 2 optional media
- Clear glass lens included
- Trim clips designed for 5/8" ceiling thickness

DETAILS


Trim Class: 4"
Category: Recessed Downlight
Shape: Round
Adjustability: Tilt




2-160-T-Demi-MR16-Specs • Subject to change without notice • Rev. 2017.07.06 • 1/4

Features & Lighting

DIMENSIONS



CEILING CUTOUT



FLANGE FINISHES


- White
- Chrome Plated
- Black
- Matte Silver
- Bronze
- Matte Nickel

2-160-T-Demi-MR16-Specs • Subject to change without notice • Rev. 2017.07.06 • 2/4


Compatible Housings

NON-INSULATED

2-020
Round Non-Insulated
L 10 1/2" [267mm]
W 7 3/4" [197mm]
H 3 1/2" [90mm]




2-060
Round Non-Insulated
L 13 3/4" [349mm]
W 10 7/8" [276mm]
H 3 1/2" [90mm]




INSULATED

2-010
Round Insulated
L 13 3/4" [350mm]
W 10 7/8" [277mm]
H 7" [178mm]




2-012
Round Insulated
L 22 1/2" [572mm]
W 8 1/2" [216mm]
H 5 7/8" [150mm]




REMODEL

2-030
Round Remodel
L 14" [356mm]
W 4 1/2" [114mm]
H 5 1/8" [130mm]




SPECIALIZED

2-060
Round Chicago Plenum
L 13 3/4" [350mm]
W 10 7/8" [277mm]
H 4 1/2" [115mm]



2-100
Round Concrete Housing
L 18" [457mm]
W 12" [305mm]
H 6" [152mm]



2-160-T Demi MR16

Project

Type

Notes

Product Code

1 2 3 4 5

1. Trim

2-160-T Demi

2. Lamp

MR16 Halogen

3. Flange Finish

01 White

02 Chrome Plated

04 Black

05 Matte Silver

06 Bronze

11 Matte Nickel

CC Custom Color¹

4. Optional Media (2 Maximum)

CL Clear

EL Elongating

FRO Frosted

HC Honeycomb

PER Perimeter Frosted

SL Solite Softening

SPDL Spread

5. Options

BC Black Center

EXT Extension Clips (Maximum 2")

Notes

¹ **CC** custom color requires consultation with Lightheaded sales personnel.

2-160-T-Demi-MR16-Specs • Subject to change without notice • Rev. 2017.07.06 • 4/4