

# Digital Audio Two-Room, Multi-Source Kit, White

AU7252-WH



The AU7252-WH is a two-room, multi-source Digital Audio Kit. Conveniently supplying all of the core components necessary to install a two-room Digital Audio System with digital and analog source accessibility, this kit comes complete with (2) [AU7010-WH](#) Digital Audio Amplified Keypads, (1) [AU7000](#) Digital Audio Distribution Module, (1) [AU7001](#) Digital Audio Input Module, (1) [AU7007-WH](#) Digital Audio Global Source Input, (1) [PW1020](#) Digital Audio Power Distribution Module, (1) [PW1060](#) Power Supply, and (1) [PW7760](#) Power Supply.

## features & benefits

- Comes complete with all core components for a two-room, multi-source Digital Audio System with digital and analog source accessibility
- Provides access to streaming services such as: Pandora, Rhapsody, Napster, SiriusXM, TuneIn, and Deezer
- Allows streaming of networked digital content from iTunes, Windows Media Player libraries, and mobile devices
- Offers global access to analog source equipment
- Provides 20 watts of Class D power per zone
- Conveniently controllable through both included keypads as well as free, intuitive Android or iOS apps for smartphones and tablets
- Provides all core components needed to install a two-room, multi-source Digital Audio System with digital and analog source accessibility
- Structured wiring based to offer easy installation and a repeatable solution
- Simple setup using smartphone or tablet, no PC required

## specifications

### General Info

Cable Type: Connect Cat5e or better and speaker wire 18-16 gauge.

Color: White

Size: 8.25" x 8.25" x 13.5"

Termination: 918.84 cu. in.

Connection Type: RJ45 connections and removeable pheonix screw down terminals

Type: Low Voltage, Audio System  
Housing Material: Plastic/Metal  
Special Features: 2-Zone, 4-Source Digital Audio System  
Style: Decorator Keypad; Structured wiring cabinet (not included)

### **Listing Agencies/Third Party Information**

RoHS: Yes  
FCC Standard: Yes  
UL Standard: Yes

### **Dimensions**

Depth U S: 13.5"  
Width U S: 8.25"  
Primary Packaging Weight Metric: 2.5 kg  
Primary Package Weight U S: 5.5 lbs  
Product Weight Metric: 2.5 kg  
Product Weight U S: 5.5 lbs  
Volume: 918.84 cu. in.  
Weight: 5.5 lbs  
Height: 8.25"

### **Technical Information**

Connection Method: Ethernet network  
Mounting: Wall Mount/Enclosure Mount  
Power Requirements: 24 VDC 60W Power Supply / 12 VDC 18W Power Supply  
Supported Standards: FCC, UL, RoHS  
Watts: 20W 8Ω  
Connection Location: Data Control Interface: Ethernet/Digital Keypad  
Source Inputs: 2-Sources  
Source Outputs: 2-Zones

### **Buy American Act Compliance**

Country of Origin: CHINA