



Part No.	Size	T in [mm]	R in [mm]	W in [mm]	A in [mm]	B in [mm]	D in [mm]
077818	2"	0.1 [3]	1.1 [29]	0.8 [20]	1.0 [25]	2.4 [60]	0.3 [7]
077819	2.5"	0.1 [3]	1.4 [37]	0.9 [23]	0.8 [20]	2.9 [74]	0.3 [7]
077820	3"	0.1 [3]	1.7 [43]	1.0 [26]	0.9 [23]	3.8 [96]	0.3 [8]
077821	3.5"	0.1 [3]	2.0 [50]	1.0 [26]	1.0 [26]	4.0 [101]	0.3 [8]
077822	4"	0.1 [3]	2.0 [52]	1.0 [26]	1.0 [26]	4.7 [120]	0.3 [8]
077823	6"	0.1 [3]	3.6 [92]	1.3 [32]	1.0 [27]	6.4 [163]	0.3 [8]
077824	5"	0.1 [3]	2.9 [74]	1.3 [32]	1.1 [29]	5.5 [139]	0.3 [8]

SIZES SHOWN ARE FOR REFERENCE 3D MODEL IS TO BE USED FOR MANUFACTURING / VERIFICATION		ALL CHANGES MUST BE APPROVED AND RECORDED BY ENGINEERING	
UNIT: INCHES UNLESS DUAL DIMENSION: INCH (METRIC)	PROJECTION 		
THIS DRAWING AND ALL TECHNICAL INFORMATION APPEARING HEREON ARE PROPERTY OF IPEX TECHNOLOGIES INC. AND MUST BE KEPT IN CONFIDENCE BY THE RECIPIENT. THE SAME MAY NOT BE USED OR REPRODUCED EITHER IN WHOLE OR IN PART WITHOUT THE EXPRESS CONSENT OF IPEX TECHNOLOGIES INC.	TITLE 2 HOLE PVC COATED STEEL PIPE STRAP		
	PAPER SIZE ANSI B	NAME Z. Liu	DATE 3/17/2018
PART APPEARANCE:	COLOR:	DRAWN	MAT'L:
SURFACE FINISHES: (UNLESS OTHERWISE NOTED)	APP'D		PRODUCT CODE:
	INSIDE:	DIMENSIONS ARE IN INCHES TOLERANCES (UNLESS OTHERWISE SPECIFIED)	
OUTSIDE:	FRACTIONAL ±.005	DECIMAL ±0.025	
OTHER:	X.XX ±0.030	X.XXX ±0.005	
FILENAME: <input checked="" type="checkbox"/>	FOLDER: <input checked="" type="checkbox"/>	ANGULAR ±2.0	