# Digital Audio Four-Room, Single-Source Kit, White

AU7154-WH



The AU7154-WH is a four-room, single-source Digital Audio Kit. Conveniently supplying all of the core compoments necessary to install a four-room Digital Audio System with digital source accessibility, this kit comes complete with (4) AU7010-WH Digital Audio Amplified Keypads, (1) AU7000 Digital Audio Distribution Module, (1) AU7001 Digital Audio Input Module, (1) PW1020 Digital Audio Power Distribution Module, (1) PW1060 Power Supply, and (1) PW7760 Power Supply.

# features & benefits

- Comes complete with all core components for a four-room, single-source Digital Audio System with digital source accessibility
- Provides access to streaming services such as: Pandora, Rhapsody, Napster, SiriusXM, Tuneln, and Deezer
- Allows streaming of networked digital content from iTunes,
  Windows Media Player libraries, and mobile devices
- Provides 20 watts of Class D power per zone
- Conveniently controllable through both included keypads as well as free, intuitive Android or ioS apps for smartphones and tablets
- Provides all core components needed to install a four-room, single-source Digital Audio System with digital source accessibility
- Structured wiring based to offer easy installation and a repeatable solution
- Simple setup using smartphone or tablet, no PC required

# specifications

#### **General Info**

Cable Type: Connect Cat5e or better and speaker wire 18-16 gauge.

Color: White

Size: 11.25" x 7.75" x 14.5" Termination: 1264.22 cu. in.

Connection Type: RJ45 connections and removeable pheonix screw down terminals

Type: Low Voltage, Audio System

Housing Material: Plastic/Metal

Special Features: 4-Zone, 1-Source Digital Audio System

Style: Decorator Keypad; Structured wiring cabinet (not included)

## **Listing Agencies/Third Party Information**

RoHS: Yes

FCC Standard: Yes UL Standard: Yes

### **Dimensions**

Depth U S: 14.5" Width U S: 11.25"

Primary Packaging Weight Metric: 2.5 kg Primary Package Weight U S: 5.5 lbs

Product Weight Metric: 2.5 kg Product Weight U S: 5.5 lbs Volume: 1264.22 cu. in.

Weight: 5.5 lbs Height: 7.75"

#### **Technical Information**

Connection Method: Ethernet network Mounting: Wall Mount/Enclosure Mount

Power Requirements: 24 VDC 60W Power Supply / 12 VDC 18W Power Supply

Supported Standards: FCC, UL, RoHS

Watts: 20W 8Ω

Connection Location: Data Control Interface: Ethernet/Digital Keypad

Source Inputs: 1-Source Source Outputs: 4-Zones

## **Buy American Act Compliance**

Country of Origin: CHINA