








Version	DT	3LD2 7 and 3LD2 8	PU (UNIT, SET, M)	PS*/ P. unit	PG	Weight per PU approx.		
		Order No.	Price per PU			kg		
<b>For front mounting</b>								
		<b>4. contact (N conductor)</b> Leading switch-on, lagging switch-off	▶	<b>3LD9 280-0B</b>	1	1 unit	103	0.101
3LD9 280-0B (left) 3LD9 280-2B (right)		<b>N or PE terminals</b> Through-type	▶	<b>3LD9 280-2B</b>	1	1 unit	103	0.092
		<b>Auxiliary switches</b> For mounting on the left and/or right, lagging switch-on, leading switch-off	▶	<b>3LD9 200-5B</b>	1	1 unit	103	0.046
3LD9 200-5B		• 1 NO + 1 NC For mounting on the left and/or right, lagging switch-on, leading switch-off, with gold-plate contacts for SIMATIC re- quest	▶	<b>3LD9 200-5BF</b>	1	1 unit	103	0.028
	C	• 1 NO + 1 NC						
<b>For floor mounting, distribution board mounting or molded-plastic enclosures</b>								
		<b>4. contact (N conductor)</b> Leading switch-on, lagging switch-off	▶	<b>3LD9 280-0C</b>	1	1 unit	103	0.102
3LD9 280-0C (left) 3LD9 280-2C (right)		<b>N or PE terminals</b> Through-type	▶	<b>3LD9 280-2C</b>	1	1 unit	103	0.093
		<b>Auxiliary switches</b> For mounting on the left and/or right, lagging switch-on, leading switch-off	▶	<b>3LD9 200-5C</b>	1	1 unit	103	0.046
3LD9 200-5C (left) 3LD9 200-6C (right)		• 1 NO + 1 NC • 2 NO For mounting on the left and/or right, lagging switch-on, leading switch-off, with gold-plate contacts for SIMATIC re- quest	▶	<b>3LD9 200-6C</b>	1	1 unit	103	0.046
	C	• 1 NO + 1 NC		<b>3LD9 200-5CF</b>	1	1 unit	103	0.028
<b>For front and floor mounting</b>								
		<b>Rotary operating mechanisms for four-hole mounting</b> Lockable in 0 position with up to 3 padlocks, including seal						
3LD9 284-1B	A	• Black		<b>3LD9 284-1B</b>	1	1 unit	103	0.154
	A	• Red/Yellow		<b>3LD9 284-3B</b>	1	1 unit	103	0.152
		<b>Switching shafts 6 x 6 mm</b> Length 300 mm	C	<b>3LD9 205-0C</b>	1	5 units	103	0.476
		Length 600 mm	C	<b>3LD9 205-2C</b>	1	5 units	103	0.476
		<b>Inscription labels</b> With English/German inscription (MAIN SWITCH/HAUPTSCHALTER)	A	<b>3LD9 286-1A</b>	1	10 units	103	0.005
3LD9 286-1A	A	Without inscription		<b>3LD9 286-4A</b>	1	10 units	103	0.054
		<b>Terminal covers as additional touch protection (also for distribution board mounting)</b> Can be snapped on at top and bottom						
3LD9 281-2A	A	• 1-pole (1 pack = 4 units)		<b>3LD9 281-2A</b>	1	4 units	103	0.007