




Quality Products. Service Excellence.

## Filterfan Rainhoods - 3R RH Series



### Application

- Type 3R / Outdoor Rainhoods
- Protection against rain and snow or large airborne debris
- Sold individually

### Features

- Easy installation
- Covers many external mounted Fans & Grills
- Fits PF2000/PF22000 thru PF5/6/7000 series Filterfans
- Tamperproof hardware and sealing gasket provided

### Standards

- UL 508A type 3R
- CSA C22.2 #94-M1

### Finish

- Cover offered in ANSI61 gray or RAL7035 light gray powder coated finish on mild steel
- Also offered in stainless steel 304 #4 finish
- Base in Galvanized sheet steel

### Grill/Solid Cover Kit

- Can be installed in bottom opening of rain hood
- Grill allows ventilation while preventing unwanted entry of large contaminants
- Solid cover allows sealing of opening when fan/filter not in use

**New and improved PDF part drawing files with more detail now available.**

Click part number in table below to access PDF, DXF, and STEP files.

Part No.	Overall Dimensions			Use with	Finish
	H	W	D		
<a href="#">RH20000GY</a>	10.44	7.77	2.17	PF2000/PF22000 Series	ANSI 61 Gray
<a href="#">RH20000LG</a>	10.44	7.77	2.17	PF2000/PF22000 Series	RAL7035
<a href="#">RH20000SS</a>	10.44	7.77	2.17	PF2000/PF22000 Series	Stainless Steel
<a href="#">RH40000GY</a>	14.57	11.71	3.35	PF25, 30, 32, 43000 Series	ANSI 61 Gray
<a href="#">RH40000LG</a>	14.57	11.71	3.35	PF25, 30, 32, 43000 Series	RAL7035
<a href="#">RH40000SS</a>	14.57	11.71	3.35	PF25, 30, 32, 43000 Series	Stainless Steel
<a href="#">RH60000GY</a>	15.88	14.66	4.33	PF5,6,7000, 65, 67000 Series	ANSI 61 Gray
<a href="#">RH60000LG</a>	15.88	14.66	4.33	PF5,6,7000, 65, 67000 Series	RAL7035
<a href="#">RH60000SS</a>	15.88	14.66	4.33	PF5,6,7000, 65, 67000 Series	Stainless Steel

### Grill/Solid Cover Kit

Part No.	Use With	Finish
<b>RHA20000G</b>	RH20000GY,LG,SS	Galvanized Steel
<b>RHA40000G</b>	RH40000GY, LG, SS	Galvanized Steel
<b>RHA60000G</b>	RH60000GY,LG, SS	Galvanized Steel

*Data subject to change without notice*

© 2021. Hammond Manufacturing Ltd. All rights reserved.