


Specialty Screwdrivers

Wire Bending Square-Recess Tip Screwdrivers – Round Shanks

Additional Feature:

- Metal stud offers a convenient and easy way to bend, loop and connect solid wire when installing outlets and switches.



661B

Cat. No.	Point Size	Shank Length	Overall Length	Bends AWG Gauges	Finish	Weight (lbs.)
661B	No. 1	4" (102 mm)	8-1/4" (210 mm)	Nos. 10, 12, 14	chrome-plated	0.20
662B	No. 2	4" (102 mm)	8-1/4" (210 mm)	Nos. 10, 12, 14	chrome-plated	0.30



5-in-1 Screwdriver/Nut Driver

Additional Feature:

- End of handle is marked to quickly identify tool.



32476

Cat. No.	Contains	Weight (lbs.)
32476	5/16" nut driver, #1 and #2 Phillips, 9/32" slotted and 3/16" slotted	.35

Replacement Bits for 5-in-1 Screwdriver/Nut Driver

Cat. No.	Fits	Description	Quantity	Weight (lbs.)
32478	5-in-1 (Cat. No. 32476)	#1 Phillips – 3/16" slotted	contains 1 bit	.036
32479	5-in-1 (Cat. No. 32476)	#2 Phillips – 9/32" slotted	contains 1 bit	.044



10-in-1 Screwdriver/Nut Driver

Additional Feature:

- End of handle is marked to quickly identify tool.



32477

Cat. No.	Contains	Weight (lbs.)
32477	5/16" and 1/4" nut drivers, #1 and #2 Phillips, 1/4" and 3/16" slotted, #10 and #15 TORX®, #1 and #2 square-recess	.35

Replacement Bits for 10-in-1 Screwdriver/Nut Driver

Cat. No.	Fits	Description	Quantity	Weight (lbs.)
32482	10-in-1 (Cat. No. 32477)	#1 Phillips – 3/16" slotted	contains 2 bits	.010
32483	10-in-1 (Cat. No. 32477)	#2 Phillips – 1/4" slotted	contains 2 bits	.012
32484	10-in-1 (Cat. No. 32477)	#1 square – #2 square	contains 2 bits	.010
32485	10-in-1 (Cat. No. 32477)	#10 Torx® – #15 Torx®	contains 2 bits	.008

TORX® is a registered trademark of Acument Intellectual Properties, LLC.



11-in-1 Screwdriver/Nut Driver

NEW!

Additional Feature:

- Integrated screwdriver/nut driver shaft holds 8 popular tips and converts to 3 nut driver sizes.
- End of handle is marked to quickly identify tool.



32500

Cat. No.	Contains	Weight (lbs.)
32500	3/8", 5/16" and 1/4" nut drivers, #1 and #2 Phillips, 1/4" and 3/16" slotted, #10 and #15 TORX®, #1 and #2 square-recess	.44

Replacement Bits for 10-in-1 Screwdriver/Nut Driver

Cat. No.	Fits	Description	Quantity	Weight (lbs.)
32482	11-in-1 (Cat. No. 32500)	#1 Phillips – 3/16" slotted	contains 2 bits	.010
32483	11-in-1 (Cat. No. 32500)	#2 Phillips – 1/4" slotted	contains 2 bits	.012
32484	11-in-1 (Cat. No. 32500)	#1 square – #2 square	contains 2 bits	.010
32485	11-in-1 (Cat. No. 32500)	T10 TORX® – T15 TORX®	contains 2 bits	.008

TORX® is a registered trademark of Acument Intellectual Properties, LLC.



All dimensions are in inches and (millimeters).

⚠WARNING: NOT insulated. Will NOT protect against electrical shock.

⚠WARNING: Always wear approved eye protection.

⚠WARNING: Do NOT use to pry or chisel.

