


Pluggable interface relays CR-M

Miniature relays

1



CR-M

- 1 Interface relay
- 2 Pluggable function module
- 3 Socket
- 4 Holder
- 5 Marker



CR-M

Type	Rated control supply voltage	Order Code	Price
Interface relays without LED 2 c/o contacts: 250 V, 12 A			
CR-M012DC2	12 V DC	1SVR405611R4000	
CR-M024DC2	24 V DC	1SVR405611R1000	
CR-M024AC2	24 V AC	1SVR405611R0000	
CR-M110AC2	110 V AC	1SVR405611R7000	
CR-M230AC2	230 V AC	1SVR405611R3000	
3 c/o contacts: 250 V, 10 A			
CR-M012DC3	12 V DC	1SVR405612R4000	
CR-M024DC3	24 V DC	1SVR405612R1000	
CR-M024AC3	24 V AC	1SVR405612R0000	
CR-M110AC3	110 V AC	1SVR405612R7000	
CR-M230AC3	230 V AC	1SVR405612R3000	
4 c/o contacts: 250 V, 6 A			
CR-M012DC4	12 V DC	1SVR405613R4000	
CR-M024DC4	24 V DC	1SVR405613R1000	
CR-M024AC4	24 V AC	1SVR405613R0000	
CR-M110AC4	110 V AC	1SVR405613R7000	
CR-M230AC4	230 V AC	1SVR405613R3000	

Type	Rated control supply voltage	Order Code	Price
Interface relays with LED 2 c/o contacts: 250 V, 12 A			
CR-M012DC2L	12 V DC	1SVR405611R4100	
CR-M024DC2L	24 V DC	1SVR405611R1100	
CR-M024AC2L	24 V AC	1SVR405611R0100	
CR-M110AC2L	110 V AC	1SVR405611R7100	
CR-M230AC2L	230 V AC	1SVR405611R3100	
3 c/o contacts: 250 V, 10 A			
CR-M012DC3L	12 V DC	1SVR405612R4100	
CR-M024DC3L	24 V DC	1SVR405612R1100	
CR-M024AC3L	24 V AC	1SVR405612R0100	
CR-M110AC3L	110 V AC	1SVR405612R7100	
CR-M230AC3L	230 V AC	1SVR405612R3100	
4 c/o contacts: 250 V, 6 A			
CR-M012DC4L	12 V DC	1SVR405613R4100	
CR-M024DC4L	24 V DC	1SVR405613R1100	
CR-M110DC4L	110 V DC	1SVR405613R8100	
CR-M024AC4L	24 V AC	1SVR405613R0100	
CR-M110AC4L	110 V AC	1SVR405613R7100	
CR-M230AC4L	230 V AC	1SVR405613R3100	



Full range of product and technical information place this part number in a search engine and download

2CDC110004C0206