


Data & AV Connectors



Data and AV Connectors		
Description	Application	Cat. No.
QuickPort® Cat 5 Connector	Voice & low-speed data	41108-R*5
QuickPort® Cat 3 Connector	Voice & low-speed data	41108-R*3
[A] QuickPort® GigaMax® Cat 5e Connector	High-speed data	5G108-R*5
QuickPort® Voice Grade 6-Conductor Connector	Voice	41106-R*6
QuickPort® Voice Grade 8-Conductor Connector	Voice	41108-R*8
[B] QuickPort® BNC Bulkhead Module, standard	CCTV & video	41084-B*F
[C] QuickPort® BNC Bulkhead Module, gold plated	CCTV & video	40832-0B°
[D] QuickPort® HDMI® Passthrough	TV, DVD, satellite, & home theater	40834-00#
QuickPort® S-Video Feedthrough	Enhanced video streams	40734-CV~
[E] QuickPort® USB A-A Connector, feedthrough	Computers & peripherals	40835-00~
[F] QuickPort® 3.5 mm Stereo, screw terminal	Computer audio	40839-S-S
[G] QuickPort® F-Connector, standard, 3.0 GHz	TV, DVD, satellite, & home theater	41084-F*F
[H] QuickPort® F-Connector, gold plated, 3.0 GHz	TV, DVD, satellite, & home theater	40831-0B°
QuickPort® RCA to 110	Advanced audio & video	40735-Rx†
QuickPort® RCA w/ black stripe	Advanced audio & video	40830-B*E
QuickPort® RCA w/ red stripe	Advanced audio & video	40830-B*R
QuickPort® RCA w/ yellow stripe [△]	Advanced audio & video	40830-B*Y
QuickPort® RCA w/ green stripe	Advanced audio & video	40830-B-V
QuickPort® RCA w/ blue stripe	Advanced audio & video	40830-B-L
QuickPort® Banana Jack Adapter, gold plated w/ black stripe	Advanced audio	40837-B*E
QuickPort® Banana Jack Adapter, gold plated w/ red stripe	Advanced audio	40837-B*R
[I] QuickPort® Binding Post Adapter, gold plated w/ black stripe	Advanced audio	40833-B*E
[J] QuickPort® Binding Post Adapter, gold plated w/ red stripe	Advanced audio	40833-B*R
QuickPort® Snap-in Blank Module	Secures unused ports	41084-B*B
[K] RCA Compression Connector (colored rings included)	CCTV & video	40985-CRU
[L] Compression F-Connector	CCTV & video	40985-CPF

Color Choices

Data and AV connectors are offered in a wide range of colors. To order colors, add suffix to Cat. No.



- △ = Minimum order quantity and lead times may apply.
- ~ = Color: White (W), Ivory (I)
- x = Inner Barrel Color: Orange (O), Red (R), White (W), Yellow (Y)
- + = Color: White (W), Light Almond (T), Ivory (I), Gray (G), Black (E)
- = Inner Barrel Color: Black (E), Yellow (Y), Red (R), Blue (L), Green (G)
- ± = Color: Choose from any of the 13 colors shown at left
- * = Color: White (W), Light Almond (T), Ivory (I), Gray (G), Black (E), Brown (B)
- ° = Color: White (W), Light Almond (T), Ivory (I)
- # = Color: White (W), Light Almond (T), Ivory (I), Black (E)

HOME 5e® & HOME 6® QuickPort® Connectors	
Description	Cat. No.
[M] HOME 5e® Connector, Standard	5EHOM-R*5
[N] HOME 6® Connector, Standard	61HOM-R*6



* = Color: White (W), Light Almond (T), Ivory (I), Blue (L), Gray (G), Black (E), Brown (B)