

Digital Audio Four-Room Expansion Kit, White

AU7054-WH



The AU7054-WH is a four-room Digital Audio Expansion Kit. Conveniently supplying all of the core components necessary to add four new rooms of audio onto an existing Digital Audio System, this kit comes complete with (4) [AU7010-WH](#) Digital Audio Amplified Keypads, (1) [AU7004](#) Digital Audio Expansion Module, (1) [PW1020](#) Digital Audio Power Distribution Module, and (1) [PW1060](#) Power Supply.

features & benefits

- Expands an existing Digital Audio System to four additional rooms
- Comes complete with all core components, including: (4) Digital Audio Amplified Keypads; (1) AU7004 Digital Audio Expansion Module; (1) PW1020 Digital Audio Power Distribution Module; and, (1) PW1060 Power Supply
- Provides 20 watts of Class D power per zone
- Compatible with Digital Audio source components for listening variety
- Conveniently controllable through both included keypads as well as free, intuitive Android or iOS apps for smartphones and tablets
- Provides all core components needed to add four new rooms to an existing system, for simplified expansion
- Simple setup using smartphone or tablet, no PC required

specifications

General Info

Cable Type: Connect Cat5e or better and speaker wire 18-16 gauge.

Color: White

Size: 8.25" x 8.25" x 13.5"

Termination: 918.84 cu. in.

Connection Type: RJ45 connections and removeable pheonix screw down terminals

Type: Low Voltage, Audio System

Housing Material: Plastic/Metal

Special Features: Digital Audio Four-Room Expansion Kit

Style: Decorator Keypad; Structured wiring cabinet (not included)

Listing Agencies/Third Party Information

RoHS: Yes
FCC Standard: Yes
UL Standard: Yes

Dimensions

Depth U S: 13.5"
Width U S: 8.25"
Primary Packaging Weight Metric: 1.98 kg
Primary Package Weight U S: 4.36 lbs
Product Weight Metric: 1.98 kg
Product Weight U S: 4.36 lbs
Volume: 918.84 cu. in.
Weight: 4.36 lbs
Height: 8.25"

Technical Information

Connection Method: Ethernet network
Mounting: Wall Mount/Enclosure Mount
Power Requirements: 24 VDC 60W Power Supply / 12 VDC 18W Power Supply
Supported Standards: FCC, UL, RoHS
Watts: 20W 8Ω
Connection Location: Data Control Interface: Ethernet/Digital Keypad
Source Outputs: Adds: 4-Zones

Buy American Act Compliance

Country of Origin: CHINA