

# Conduit Clamps and Straps

Support conduit on walls and structures.

## Pipe Straps

- Available in malleable iron/stamped steel with nominal .015" (15 mils) PVC coating in your choice of blue, white or grey.
- Choose one- or two-hole versions.
- Sized to allow for the extra thickness of the PVC coating.



## PVC-Coated Pipe Straps

Cat. No.		Pipe Size in. (mm)
One-Hole Malleable Iron	Two-Hole Stamped Steel	
1HMS1/2- <sub>  </sub>	2HS1/2- <sub>  </sub>	1/2 (16)
1HMS3/4- <sub>  </sub>	2HS3/4- <sub>  </sub>	3/4 (21)
1HMS1- <sub>  </sub>	2HS1- <sub>  </sub>	1 (27)
1HMS1-1/4- <sub>  </sub>	2HS1-1/4- <sub>  </sub>	1-1/4 (35)
1HMS1-1/2- <sub>  </sub>	2HS1-1/2- <sub>  </sub>	1-1/2 (41)
1HMS2- <sub>  </sub>	2HS2- <sub>  </sub>	2 (53)
1HMS2-1/2- <sub>  </sub>	2HS2-1/2- <sub>  </sub>	2-1/2 (63)
1HMS3- <sub>  </sub>	2HS3- <sub>  </sub>	3 (78)
1HMS3-1/2- <sub>  </sub>	2HS3-1/2- <sub>  </sub>	3-1/2 (91)
1HMS4- <sub>  </sub>	2HS4- <sub>  </sub>	4 (103)

Metric size designator (ANSI C80.1-1994).

Cat. No.	Pipe Size in. (mm)
CB1/2- <sub>  </sub>	1/2 (16)
CB3/4- <sub>  </sub>	3/4 (21)
CB1- <sub>  </sub>	1 (27)
CB1-1/4- <sub>  </sub>	1-1/4 (35)
CB1-1/2- <sub>  </sub>	1-1/2 (41)
CB2- <sub>  </sub>	2 (53)
CB2-1/2- <sub>  </sub>	2-1/2 (63)
CB3- <sub>  </sub>	3 (78)
CB3-1/2- <sub>  </sub>	3-1/2 (91)
CB4- <sub>  </sub>	4 (103)

Metric size designator (ANSI C80.1-1994).

Use as spacers with one-hole pipe straps.

## Ocal PVC-Coated Clamp-Back Spacers

- Provides space for air flow between conduit and mounting surface.
- Nominal .015" (15 mils) PVC coating for corrosion protection.



Cat. No.	Colour
<b>CB1-<sub>  </sub></b>	<b>—</b>
— = space for colour identifier	
<b>G</b> =	Grey
<b>W</b> =	White
<b>B</b> =	Blue
<b>R</b> =	Red

Custom colours also available - Std. min. quantities are required. Please contact your Regional Sales Office.