



**Signal/auxiliary contacts**

Function: choice through a selector between indication of the position of the device's contacts and signalling of the fault (overcurrent/short-circuit for MCBs and RCBOs; earth fault for RCCBs and RCBOs). Suitable for MCBs S 200 series, RCCBs F 200 series, RCBOs DS 200 series.

Description	Order details Type code	Order code	Bbn 4016779 EAN	Price 1 piece	Price group	Weight 1 piece kg	Pack unit pc.
Signal contact/ auxiliary switch	<b>S 2C-S/H6R</b>	2CDS200922R0001	<b>563819</b>			0.04	1

**Auxiliary contacts**

Function: indication of the position of the device's contacts. Suitable for MCBs S200 series. To be mounted on the left side of the MCB thanks to the special pin (max 1 contact per MCB).

Description	Order details Type code	Order code	Bbn 4016779 EAN	Price 1 piece	Price group	Weight 1 piece kg	Pack unit pc.
Auxiliary contact	<b>S 2C-H6R</b>	2CDS200912R0001	<b>563826</b>			0.04	1
Auxiliary contact 1 NO/1NC	<b>S2C-H11L</b>	2CDS200936R0001	<b>648820</b>			0.04	1
Auxiliary contact 2 NO	<b>S2C-H20L</b>	2CDS200936R0002	<b>648837</b>			0.04	1
Auxiliary contact 2 NC	<b>S2C-H02L</b>	2CDS200936R0003	<b>648844</b>			0.04	1

**Bottom-fitting auxiliary contact for S 200, S 200 M, S 200 P**

1 NC	<b>S 2C-H01</b>	2CDS 200 970 R0001	<b>64551 5</b>			0.01	1
1 NO	<b>S 2C-H10</b>	2CDS 200 970 R0002	<b>64552 2</b>			0.01	1

**packing unit 15 parts**

1 NC	<b>S 2C-H01 15x</b>	2CDS 200 970 R0011	<b>64677 2</b>			0.01	15
1 NO	<b>S 2C-H10 15x</b>	2CDS 200 970 R0012	<b>64681 9</b>			0.01	15

**Shunt trip**

Function: remote opening of the device when a voltage is applied. Suitable for MCBs S 200 series and RCBOs DS 200 series.

Shunt trip							
AC/DC 12...60 V	<b>S 2C-A1</b>	2CDS200909R0001	<b>570992</b>			0.15	1
AC 110...415 V/ DC110...250 V	<b>S 2C-A2</b>	2CDS200909R0002	<b>571005</b>			0.15	1

**Undervoltage release**

Function: protection of the load in the event of a voltage drop (between 70% and 35% of its rated value); positive safety (device's tripping when the voltage is disconnected) emergency stop by means of a button. Suitable for MCBs S 200 series, RCBOs DS 200 series.

Description	Order details Type code	Order code	Bbn 8012542 EAN	Price 1 piece	Price group	Weight 1 piece kg	Pack unit pc.
12VDC	<b>S2C-UA 12 DC</b>	2CSS200911R0001	<b>839705</b>			0.09	1
24VAC	<b>S2C-UA 24 AC</b>	2CSS200911R0002	<b>839804</b>			0.09	1
24VDC	<b>S2C-UA 24 DC</b>	2CSS200911R0007	<b>896401</b>			0.09	1
48VAC	<b>S2C-UA 48 AC</b>	2CSS200911R0003	<b>839903</b>			0.09	1
48VDC	<b>S2C-UA 48 DC</b>	2CSS200911R0008	<b>896500</b>			0.09	1
110VAC	<b>S2C-UA 110 AC</b>	2CSS200911R0004	<b>840008</b>			0.09	1
110VDC	<b>S2C-UA 110 DC</b>	2CSS200911R0009	<b>896609</b>			0.09	1
230VAC	<b>S2C-UA 230 AC</b>	2CSS200911R0005	<b>840107</b>			0.09	1
230VDC	<b>S2C-UA 230 DC</b>	2CSS200911R0010	<b>896708</b>			0.09	1
400VAC	<b>S2C-UA 400 AC</b>	2CSS200911R0006	<b>840206</b>			0.09	1