

Utility Boxes and Covers











CI1141

BC1110

CI1110-SB

BC1110-LSKO

BC1110-SSX



BC1110-R



BC1151

BC1151: For toggle switch.

BC1199

BC1199: For duplex receptacle.



















BC11-C-1

BC11-C-2

BC11-C-3

BC11-C-4

BC11-C-5

BC11-C-10

CI11-C-10-HV

BC11-C-4-HV

BC11-C-5-HV



Oat Na	Volume (Cu. in.)	Features		Knockouts		
Cat. No.		Bracket	Raised Ground Screw	1/2 in. ends	1/2 in. bottom	1/2 in. sides
1-1/2 in. Deep – 4 in. x 2-1/	4 in.					
CI1141	13.0	mounting lugs	no	2	2	6
1-7/8 in. Deep - 4 in. x 2-3/8	3 in.					
BC1110	16.5	-	yes	2	2	6
CI1110-SB	16.5	"SB"	yes	2	2	3
BC1110-R	16.5	-	-	2	-	6
2-1/8 in. Deep - 4 in. x 2-1/2	2 in.					
BC1151	18.5	-	no	2	2	-
BC1199	18.5	-	no	2	2	-
1-7/8 in. Deep - 4 in. x 2-3/8	3 in.					
BC1110-LSKO	16.5	-	yes	2	2	-
BC1110-SSX	16.5	"SSX"	ves	2	2	_

Cat. No.	Description	Cat. No.	Description	
Covers - 11	Series			
BC11-C-1	For duplex receptacle	BC11-C-10	Decora/GFCI	
BC11-C-2	For 1-19/32 in. diameter 20 A single locking receptacle	CI11-C-10-HV	Decora 347 volt	
BC11-C-3	For 1-13/32 in. diameter 15 A single receptacle	BC11-C-4-HV	Blank 347 volt	
BC11-C-4	Blank	BC11-C-5-HV	For toggle switch	
BC11-C-5	For toggle switch 347 volt	Note: Covers: Device m	Note: Covers: Device mounting screws included	



347 Volt Boxes

Covers







BC11-C-4-HV



BC11-C-5-HV



CI11-C-10-HV



CIFS-1G-1/2-HV CIFS-1G-3/4-HV





CIFS-9-HV



Cat. No.	Volume (Cu. in.)	Number of Gangs	Dimensions	Features	Knockouts
Oat. No.			H x W x D (in.)	Raised Ground Screw	1/2 in. ends
1-7/8 in. Deep					
CI1110-HV	16.5	1	4 x 2-3/8 x 1-7/8	yes	2
347 Volt "FS" Box Kits — 1-7/8 in. Deep (Cast Aluminum)					
CIFS-1G-1/2-HV	14.0	1	6 x 2-13/16 x 1-7/8	yes	1 x 1/2 hub
CIFS-1G-3/4-HV	14.0	1	6 x 2-13/16 x 1-7/8	yes	1 x 3/4 hub

Note: All HV boxes have tapped holes spaced 3-17/32 in. to accommodate 347 Volt switches.

Cat. No.	Description		
347 Volt Utility Box Covers			
BC11-C-4-HV	Blank		
BC11-C-5-HV	One toggle switch		
CI11-C-10-HV	Decora		

Cat. No.	Description		
347 Volt "FS" Cover (Stamped Aluminum)			
CIFS-9-HV	One toggle switch		

Mounting screws included

