

# WiFi Color Indoor Monitor

7-inch Touch Screen



## System Overview

The DHI-VTH5221-S Series indoor monitors allow tenants to view and talk with visitors, record call sessions, monitor the surroundings from outdoor stations and IP cameras and remotely unlock doors. Visitors can also leave messages, which can be retrieved from the indoor monitor. The DHI-VTH5221-S Series indoor monitors are used as part of a video intercom solution with compatible outdoor stations.

## SIP Compatibility

Dahua Intercom devices are compatible with the Session Initiation Protocol version 2.0 (SIP), a signaling protocol for Internet conferencing, telephony, presence, event notification, and instant messaging. SIP is widely used to initiate and terminate Voice Over Internet Protocol (VOIP) calls, as well as connect physical devices to mobile applications. Dahua Intercom devices are ideal for single-family homes as well as large residential complexes or commercial properties.

## **Technical Specification**

System			
Main Processor	Embedded Micro Processor		
Operating System	Embedded Linux		
Display			
Viewing Area	7-in. TFT, Capacitive		
Resolution	1024 x 600 (WVGA)		
Input	Touchscreen Display		
Interface			
Audio	Input: Omnidirectional Microphone Output: Built-in Speaker Two-way Talk		
	Two way talk		
Audio Compression	G.711		
Audio Compression Wired Zones			
	G.711		
Wired Zones	G.711 Six (6) On-board Zones		
Wired Zones Wireless Zones	G.711 Six (6) On-board Zones Eight (8)		

- 7-inch Capacitive Touch Screen, 1024 x 600 Resolution
- Simplified Connection and Setup
- Supports Alarm Integration with 3rd Party Intrusion Devices
- Monitor up to 32 IP Cameras
- Integrated Micro SD Card Slot, maximum 32 GB
- Perform Call Session Recordings and Take Snapshots of Live Video (requires SD card)
- WiFi-enabled and PoE Power Supply
- Setup and Activate up to Six Alarm Inputs and One Alarm Output
- Surface-mounted



## Network

Video Compression	H.264			
WiFi	IEEE 802.11b/g/n			
Ethernet	10/100 Mbps, Self-adaptive			
Network Protocol	TCP/IP			
Third-party Camera Support	ONVIF H.264 Cameras, maximum resolution of 720p			
Management Software	DSS Express/Pro			
Certifications				
Electromagnetic Compatibility (EMC)	FCC CFR 47 Part 15 subpart B ANSI C63.4 - 2009 EN 55022:2010, EN 55024:2010, EN 50130-4:2011, EN 61000-6-3:2007, EN 61000-3-2:2006+A1:2009 EN 61000-3-3:2008, IEC 61000-4-2:2008, IEC 61000-4-3:2010, IEC 61000-4-4:2012, IEC 61000-4-5:2005, IEC 61000-4-6:2008, IEC 61000-4-8:2009, IEC 61000-4-11:2004			
Electrical				
Power	12 VDC or PoE (802.3af) Requires a separate 12 VDC power supply, or power via a PoE switch.			
Power Consumption	Standby: < 5 W Operation: < 7 W			
Environmental				
Operating Temperature	-10° C to +55° C (14° F to +131° F)			
Operating Humidity	10% to 90%, Relative			
Construction				
Dimensions	215.0 mm x 140.0 mm x 21.0 mm (8.46 in. x 5.51 in. x 0.83 in.)			
Net Weight	0.80 kg (1.76 lb)			
Installation	Surface-mount			

## Intercom | DHI-VTH5221DW-S / DHI-VTH5221D-S

## **Outdoor Station Compatibility**

The DHI-VTH5221-S Series Indoor Monitors can be used with the following Video Intercom Outdoor Stations:

DHI-VTO2111D-WP-S	WiFi Outdoor Station with mobile app compatibility
DHI-VTO2000A-S	IP Outdoor Station with mobile app compatibility
DHI-VTO1210C-X-S	IP Outdoor Station (Stainless Steel Panel)

Ordering Information				
Туре	Part Number	Description		
WiFi	DHI-VTH5221DW-S	7-in. Capacitive Touchscreen Color WiFi Monitor, White Bezel (Includes 4GB Micro SD Card)		
Monitor	DHI-VTH5221D-S	7-in. Capacitive Touchscreen Color WiFi Monitor, Black Bezel (Includes 4GB Micro SD Card)		
Accessories, optional	ADS-12AM-12 12012EPCU	12 VDC, 1 A Power Adapter for DHI-VTH5221D-S/DW-S		
	DH-PFS3006-4ET-60	4-Port PoE Ethernet Switch		
	DH-PFS3010-8ET-96	8-Port PoE Ethernet Switch		
Accessories				

## Optional









ADS-12AM-12 12012EPCU 12 VDC, 1 A Power Adapter for use with DHI-VTH5221-S Series

DH-PFS3006-4ET-60 4-Port PoE Ethernet Switch

DH-PFS3010-8ET-96 8-Port PoE Ethernet Switch

## Dimensions (mm/in.)






## Intercom | DHI-VTH5221DW-S / DHI-VTH5221D-S

## Applications

#### **IP** - Apartment Solution

WiFi - Home Solution



6 Electric Lock

Public net

8

Electric Lock

Rev 001.005 © 2019 Dahua Technology USA Inc. All rights reserved. Design and specifications are subject to change without notice.

Detector

VTH2

0 -

8 Electric Lock

IP

Wi-Fi